

PLUG-IN RELAY COMPACT UNIT 24V AC, 2 CO LED  
MODULE RED SOCKET W. LOGIC ISOLATION PLUG-  
IN TERMINAL (PUSH-IN)

### General technical data:

Supply voltage frequency for auxiliary and control current circuit Rated value		
• minimum	Hz	50
• maximum	Hz	60
<b>Type of voltage</b>		AC
<b>Control supply voltage</b>		
• with AC		
— at 50 Hz Rated value		
— minimum	V	24
— maximum	V	24
— at 60 Hz Rated value		
— minimum	V	24
— maximum	V	24
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		2
Operating current of the auxiliary contacts		
• at AC-15		
— at 230 V	A	2.5
<b>Design of the switching function positively driven</b>		No
<b>Switching behavior</b>		monostable

### Mechanical data:

<b>Type of electrical connection</b>		spring-loaded terminals
<b>Design of the relay operating mechanism</b>		poled
<b>Product component Plug-in socket</b>		Yes
<b>Width</b>	mm	15.5
<b>Height</b>	mm	71
<b>Depth</b>	mm	98

### Certificates/ approvals:



[Declaration of Conformity](#)

#### Further information

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=LZS:RT4D4R24>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/LZS:RT4D4R24>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=LZS:RT4D4R24&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=LZS:RT4D4R24&lang=en)

last modified:

15.01.2015