

1534807-1 ✓ ACTIVE

AMPLIMITE

TE Internal #: 1534807-1

Cable Clamp Kit, Zinc, Shell Size 2, Shielded, 15 Position

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp Kit**

Primary Product Material: **Zinc**

Compatible With Connector Shell Size: **2**

Shielded: **Yes**

Number of Positions: **15**

Features

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
------------------------------	-----------------

Configuration Features

Number of Positions	15
---------------------	----

Body Features

Cable Exit Angle	45°
Primary Product Material	Zinc

Mechanical Attachment

Thread Size	14702
-------------	-------

Housing Features

Compatible With Connector Shape	D-Shaped
Body Orientation	Straight

Dimensions

Compatible Insulation Diameter Range	4.8 – 11 mm [.189 – .433 in]
--------------------------------------	------------------------------

Operation/Application

--	--



Compatible With Connector Shell Size	2
Shielded	Yes

Packaging Features

Packaging Method	Bag
Packaging Quantity	10

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1534808-1
HD20 COVER KIT15POS FOR
FERRULES

Customers Also Bought



TE Part #3-1625999-6
HSC100 47R 5%



TE Part #1-2308340-7
FULL METAL HOODS SIZE 1-7 (RAW
135 DEG)



TE Part #1-770834-0
MINI UMNL SOK AU LF



TE Part #2-1614884-6
CPF 0805 24R 0.1% 25PPM 1K RL



TE Part #8-328527-1
TERMINAL,PG R 16-14 8



TE Part #1534805-1
HD20 COVER KIT 9POS WITH CABLE



TE Part #103649-E
ERBIC BUS D BUS-SYSTEM SYS PROF
HO AB CU



TE Part #ASA020N00400235000
623 PLUG



TE Part #ASA055N00390235000
623 PLUG

Documents

Product Drawings

HD20 COVER KIT 15P

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1534807-1_B1.2d_dxf.zip



English

Customer View Model

[ENG_CVM_1534807-1_B1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1534807-1_B1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

German

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English