




### Description

The M1575HCT-22P-SMA is a rugged high performance passive antenna designed for the GPS L1 band, and built on Maxtena proprietary Helicore® technology. This technology provides exceptional pattern control, polarization purity and high efficiency in a very compact form factor. The M1575HCT-22P-SMA is a screw-on design, featuring an integrated SMA connector. The ultra light design is rated IP-67 when both mounted and unmounted for added protection. This product is designed for applications requiring high quality reception of GPS signals.

# **Mechanical Specifications**

dimensions are in mm



## **Electrical Specifications**

Parameter	Design Specifications
Frequency	1575 MHz
Polarization	RHCP
Antenna element peak gain	-0.5 dBic (typical)
Efficiency	25% (typical)
Bandwidth (-1dB)	20 MHz
Axial Ratio	1 dB (typical) / 1.5 dB (max)
VSWR	1.5 (max)
Impedance	50 Ohm
Operating temp.	from -40°C to 85°C
RF connector	SMA
Overall dimensions	38 mm (height) x 18.50 mm (diameter)
Weight	10 grams




### **Features**

- · GPS band
- · Very low axial ratio
- IP-67 mounted and unmounted
- Ultra light weight 10 grams
- · Ground plane indepedent

## Applications

- · Vehicle and fleet tracking
- Military & security
- Asset tracking
- Seismic recording instruments
- · Oil & gas industries
- Navigation devices
- Mining equipment
- LBS & M2M applications
- · Handheld devices

#### Realized gain plot Measured at 1575 MHz



Maxtena Inc. 7361 Calhoun Place, Suite 102 Rockville, MD 20855 1-877-629-8362 info@maxtena.com

www.maxtena.com



Rev 1.0 | Issue Date: July 3rd 2014 | © 2014 Maxtena Inc, all rights reserved