

PCBN clamp holder, negative, right

For longitudinal turning using CN indexable insert

ATORN[®]

Application


For longitudinal turning using CN indexable insert 80°.

Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type C, 75° pitch angle, 80° tip angle, 0° clearance angle

Advantage

- extremely stable geometry for longitudinal machining with large feed depths and challenging conditions
- negative body geometry ensures good stability and absorption of force for large cutting depths



| | |
|---------------------------------------|-------------------|
| Art. No. | 17837 110 |
| ISO name | PCBN R/L 2020 K12 |
| Shaft height | 20 mm |
| Shank width | 20 mm |
| Length | 125 mm |
| Length of head | 28 mm |
| Programming size | 22 mm |
| Suitable for indexable inserts | CN.. 1204.. |
| Tool design | Right |
| DIN | 4983 |

EAN-Code

4050293127409