

air hydraulic pump

ATORN®

Application

to open hydraulic clamping modules or clamping stations.

Version

- Compact, compressed air operated hydraulic pump for single-acting circuits. The pump is equipped with a built-in safety valve which controls the hydraulic output pressure. the factory default setting of the safety valve is max. operating pressure of 60 bar. through the expansion body in the oil tank, the pump can be used horizontally and vertically. connecting thread air: G1/4 connecting thread oil: G1/4



Art. No.	28981 535
Min./max. air pressure	4-6 bar
Effective oil volume	1000 cm ³
Max. feed quantity	0.75 l/min
Weight	5.9 kg

EAN-Code

4050293319484