




ErgoPro Series Finishing Tools
Outils de Finition, Série "ErgoPro"
Werkzeuge zur Oberflächenbearbeitung der Baureihe ErgoPro
Herramientas de Acabado - Serie ErgoPro
Utensili per la Finitura - Serie ErgoPro

Angle grinders
 Meuleuses d'angle
 Winkelschleifmaschinen
 Amoladoras angulares
 Smerigliatrici ad angolo

ErgoPro



77A60P107M-EU



Specifications at 90 psi – Caractéristiques à 6,2 bar – Technische Daten bezogen auf 6,2 bar – Especificaciones a 6,2 bar – Caratteristiche a 6,2 bar

Ref.	kWatt	1 min.						AIR	AIR
	kW	rpm	mm	in	kg	mm	mm	in (NPT)	mm
77A60P107M-EU	1.10	6 000	Ø 180 - Type 27	5/8" - 11	4.09	446	99	3/8	13
77A60P109M-EU	1.10	6 000	Ø 230 - Type 27	5/8" - 11	4.18	446	99	3/8	13
77A75P107M-EU	1.10	7 500	Ø 180 - Type 27	5/8" - 11	4.18	446	99	3/8	13



ErgoPro

88V60P109M-EU

ErgoPro

99V60S106M-EU


99V60P109M-EU

ErgoPro



ErgoPro

Vertical grinders
 Meuleuses verticales
 Vertikalschleifmaschinen
 Amoladoras verticales
 Smerigliatrici verticali



Specifications at 90 psi – Caractéristiques à 6,2 bar – Technische Daten bezogen auf 6,2 bar – Especificaciones a 6,2 bar – Caratteristiche a 6,2 bar

Ref.	kWatt	1 min.						AIR	AIR
	kW	rpm	mm	in	kg	mm	mm	in (NPT)	mm
88V60P107M-EU	1.56	6 000	Ø 180 - Type 27	5/8" - 11	3.98	155		1/2	19
88V60P109M-EU	1.56	6 000	Ø 230 - Type 27	5/8" - 11	4.12	155		1/2	19
88V85P107M-EU	1.64	8 500	Ø 180 - Type 27	5/8" - 11	3.98	155		1/2	19
99V60P107M-EU	2.24	6 000	Ø 180 - Type 27	5/8" - 11	5.11	175		1/2	19
99V60P109M-EU	2.24	6 000	Ø 230 - Type 27	5/8" - 11	5.14	175		1/2	19
99V85P107M-EU	2.24	8 500	Ø 180 - Type 27	5/8" - 11	5.14	175		1/2	19
88V60S106M-EU	1.57	6 000	Ø 150 - Type 11	5/8" - 11	3.81	155		1/2	19
99V45S106M-EU	1.87	4 500	Ø 150 - Type 11	5/8" - 11	4.89	175		1/2	19
99V60S106M-EU	2.24	6 000	Ø 150 - Type 11	5/8" - 11	4.89	175		1/2	19

Options



Piped-away exhaust kit, part no. **88V60-K184** (88V) **99V60-K184** (99V)
 Kit d'échappement canalisé réf. **88V60-K184** (88V) **99V60-K184** (99V)
 Abluft-Ableitsatz Teile Nr. **88V60-K184** (88V) **99V60-K184** (99V)
 Juego escape remoto no. **88V60-K184** (88V) **99V60-K184** (99V)
 Kit tubo scarico aria a distanza no. **88V60-K184** (88V) **99V60-K184** (99V)