


No.	Changes and/or Note No.	Date	Sign	No.	Changes and/or Note No.	Date	Sign



UNIT: (mm)

DIMENSIONS

Size:	A	B	C	D	Part No:
09P	30.80	24.99	16.92	19.20	2101-0200-01
15P	39.15	33.32	25.25	27.70	2101-0200-02
25P	53.00	47.04	38.96	41.10	2101-0200-03
37P	69.30	63.50	55.42	57.30	2101-0200-04
50P	66.92	61.11	52.94	55.35	2101-0200-05

MATERIAL SPECIFICATIONS:

Shell: Steel, Tin or Ni Plated (With Dimples)
Zinc Plated (Without Dimples)
Insulator: Glass Filled PBT, UL 94 V-0
Contacts: Brass, Machined Pins
Gold over Nickel
Rivet: Copper-Alloy, Ni Plated

TECHNICAL SPECIFICATIONS:

Current Rating: 5 Amp
Contact Resistance: 15 mΩ Max.
Insulator Resistance: 1000 MΩ Min.
Test Voltage: 500V AC for 1 Minute
Operating Temperature: -55°C to +105°C
Recommended AWG: 24-28

DATE 2011-06-10	DRAWN MRR	SCALE	MATERIAL TYPE
	APPROVED		REPLACES
DMxx-SP Sub-D Male, Solder Cup			DRAWING No. 2101-0200-0x