


1	2		3	4	5	6	7	8
REVISIONS								
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE						



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER QQ-B-626
2. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
3. PHOSPHOR BRONZE PER QQ-B-750
4. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
5. TEFLON MIL-P-19468

4	BODY	NOTE 1	NOTE 2	1	N7900-4
3	CONTACT PIN	NOTE 3	NOTE 4	1	RSA-3477-3
2	INSULATOR	NOTE 5	NATURAL	1	RSA-3477-2
1	HOUSING	NOTE 1	NOTE 2	1	RSA-3477-1-B
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.

DIMENSIONS ARE IN MILLIMETERS
UNLESS OTHERWISE SPECIFIED TOLERANCES

0.5-6	= ±0.2
6-30	= ±0.4
30-120	= ±0.6
120-315	= ±1
315-1000	= ±1.6
1000-2000	= ±2.4

PART NO.		NF-SMAF-NT3G-50	
APPROVED	DATE	10-11-01'	
CHECKED	DATE	10-11-01'	
DRAWN	DATE	10-11-01'	
SCALE		4/1	
ISSUE		A	
FILE NO.			

Amphenol	
TITLE SMA FEMALE TO N FEMALE ADAPTOR	
DRAWING NO. KJ-NF-SMAF-NT3G-50	
ITEM NO.	

1	2		3	4	5	6	7	8
---	---	--	---	---	---	---	---	---