

ANT795-4MB IWLAN antenna with omni-directional characteristic, radial rotatab., with additional joint, incl. RSMA connector: 2/3 dBi, IP65 (-20-+60°C), 2.4/5 GHz; Wi-Fi Compliance and Please note national approvals; mounting direct to SCALANCE W with RSMA connection tech. ; scope of supply: 1x ANT795-4MB, Compact Manual on paper german/english



Wireless frequencies	
Type of mobile network / is supported	WLAN
Operating frequency	
<ul style="list-style-type: none"> <li>• for WLAN in 2.4 GHz frequency band</li> </ul>	2.4 ... 2.5 GHz
<ul style="list-style-type: none"> <li>• for WLAN in 5 GHz frequency band 1</li> </ul>	5.15 ... 5.85 GHz
Electrical data	
Impedance	50 Ω
Polarization	linear vertical
Radiation characteristic	omnidirectional
Antenna gain compared to spherical radiator	
<ul style="list-style-type: none"> <li>• of the WLAN antenna / in the 2.4 GHz frequency band</li> </ul>	2 dB
<ul style="list-style-type: none"> <li>• of the WLAN antenna / in the 5 GHz frequency band</li> </ul>	3 dB
Standing wave ratio (VSWR) / maximum	2
Radiating angle of the antenna	
<ul style="list-style-type: none"> <li>• in the 2.4 GHz frequency band / horizontal</li> </ul>	360°
<ul style="list-style-type: none"> <li>• in the 5 GHz frequency band / horizontal</li> </ul>	360°
Number of electrical connections / of the antenna	1

Type of electrical connection / of the antenna	R-SMA Connector
Design of plug-in connection	male, variable 0-90°
Angle of inclination / downward / maximum	0°

### Mechanical data

Material	
<ul style="list-style-type: none"> <li>of outer shell</li> </ul>	Polycarbonate

### Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> </ul>	-20 ... +65 °C -30 ... +70 °C
Protection class IP	IP65

### Design, dimensions and weight

Height	114 mm
Diameter	12.9 mm
Net weight	21.5 g
Mounting type	
<ul style="list-style-type: none"> <li>mast mounting</li> <li>wall mounting</li> <li>roof mounting</li> <li>directly on the device</li> </ul>	No No No Yes

### Product properties, functions, components / general

Product feature / silicon-free	No
--------------------------------	----

### Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> <li>RoHS conformity</li> </ul>	Yes
Wireless approval	Current national approvals can be found on the Internet under <a href="http://www.siemens.com/funkzulassungen">www.siemens.com/funkzulassungen</a>

### Accessories

### Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> <li>to website: Selector SIMATIC NET SELECTION TOOL</li> <li>to website: Industrial communication</li> <li>to website: Industry Mall</li> <li>to website: Information and Download Center</li> <li>to website: Image database</li> <li>to website: CAx Download Manager</li> <li>to website: Industry Online Support</li> </ul>	<a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a> <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a> <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a> <a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a> <a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a> <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a> <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

**last modified:** 08/28/2017