

Features

Universal 85V AC to 264V AC or 120V DC to 370V DC input voltage

RoHS

Compliant

- · Accepts AC or DC input (dual-use of same terminal)
- Operating ambient temperature range: -40°C to +70°C
- High I/O isolation test voltage up to 4000V AC
- Industrial product technology design
- · Over-voltage class III (Designed to meet EN61558 safety standards)
- · Low standby power consumption, high efficiency
- Low ripple & noise
- · Output short circuit, over-current, over-voltage protection
- Withstand 300V AC surge input for 5s
- UL/EN/IEC62368 safety approved
- DIN rail TS35X7.5/ TS35X15 mountable

This is AC-DC series featuring a cost-effective, energy efficient solution for standard DIN-rail mounting. The products offer a high level of stability and immunity to noise, compliant with international IEC62368 standards for EMC and safety sepecifitions meet IEC/EN61000-4, CISPR32, EN55032, UL62368, IEC62368 and EN62368. These light weight AC-DC converters also have an extremely compact design for space saving and are ideal for applications such as industrial control equipment machinery and all kinds of applications in a harsh environment.

Selection	Guide					
Certification	Part No.*	Output Power (W)	Nominal Output Voltage and Current (Vo/Io)	Output Voltage Adjustable Range(V)*	Efficiency at 230V AC (%) Typ.	Max. Capacitive Load (µF)
	MP-LI60-20B05PR2	32.5	5V/6.5A	4.9-5.5	84	20000
UL/CE/CB	MP-LI60-20B12PR2	54	12V/4.5A	10.8-13.8	88	10000
UL/CE/CB	MP-LI60-20B24PR2	<u> </u>	24V/2.5A	21.6-29	90	4000
	MP-LI60-20B48PR2	60	48V/1.25A	43.2-55.2	91	680

Note: * The actual adjustment range may extend outside the values stated, care should be exercised to ensure that the output voltage and power levels remain within the published maximum values.

Input Specifications

Item	Operating Conditions	Min.	Тур.	Max.	Unit
Innut voltage Denge	AC input	85		264	
Input voltage Range	DC input	120] -	370	
Input Frequency		47	1	63	Hz
Input Current	115V AC			1.2	
Input Current	230V AC	7 -		0.8] _
Inruch Current	115V AC		30	-	A
Inrush Current	230V AC		60	-	1
Leakage Current	264V AC		0.25mA RMS	S max.	
Hot Plug			Unavaila	ble	

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Output Specifications

Item	Operatii	ng Conditions	Min.	Тур.	Max.	Unit
Output Voltage Accuracy	0% to 100% load			±2		
Line Regulation	Rated load		-	±0.5	-	%
Load Regulation	230V AC			±1.5		
		5V Output			100	
	20MHz bandwidth	12V Output			400	
Output Ripple & Noise*	(peak-to-peak	15V Output			120 150 240 2 - 0.3 0.4 uous, self-recove	mV
	value)	24V Output	-	-		
		48V Output			240	
Temperature Coefficient		·		±0.02	-	%/°C
		5V/12V/15V/24V Output			0.3	
Stand-by Power Consumption	230V AC Input	48V Output			0.4	W
Short Circuit Protection			Hiccup,	continuou	is, self-rec	overy
Over-current Protection			≥12	0 % lo, se	, self-recovery	
	5V Output		≤7.5V (Output voltage clamp or hiccup)			
	12V Output		≤16V (Outp	out voltage	e clamp o	r hiccup)
Over-Voltage Protection	15V Output		≤20V (Outp	out voltage	e clamp o	r hiccup)
	24V Output		≤36V (Outp	out voltage	e clamp o	r hiccup)
	48V Output		≤60V (Outp	out voltage	e clamp o	r hiccup)
Minimum Load			0	-	-	%
Start-up Delay Time			-	-	3	s
· · · · · · ·	115V AC			15		
Hold-up Time	230V AC		-	80	-	ms
Note: *Ripple & noise are mea parallel capacitor.	sured at 20MHz of ba	andwidth by using a 12" twis	ted pair-wire to	erminated	I with a 0.	1uf & 47uf

General Specifications

ltem	Item		Operating Conditions		Тур.	Max.	Unit
Isolation Test	Input-output	Electric Strength T Leakage current<		4000	-	-	V AC
Operating Temper	ature			-40	-	+70	°C
Storage Temperat	ure			-40		+85	
Storage Humidity				-	-	95	%RH
Operating Altitude			·	-	-	2000	m
Switching Freque	ncy		·	-	65	-	kHz
			5V/12V/48V Output	3			
		-40°C to -30°C	24V Output	7			%/°C
Power Derating			15V Output	8	-	-	%/C
		+45°C to +70°C	·	2			
	Ī		85V AC to 100V AC		1		%/V AC



Item	Operating Conditions	Min.	Тур.	Max.	Unit
Safety Standard		UL62368	/EN62368/I	EC62368	
Safety Certification		UL62368	/EN62368/I	EC62368	
Safety Class		CLASS I	I		
MTBF	MIL-HDBK-217F@25°C	> 300,000) h		

Mechanical Specifications	
Casing Material	Plastic, heat-resistant (UL94V-0)
Package Dimensions	92.66mm × 52mm × 58mm
Weight	175g (Тур.)
Cooling Method	Free air convection

Electrom	agnetic Compa	tibility (EMC)		
Emissions	CE	CISPR32/EN55032	CLASS B	
Emissions	RE	CISPR32/EN55032	CLASS B	
	ESD	IEC/EN61000-4-2	Contact ±6KV/ Air ±8KV	perf. Criteria A
	RS	IEC/EN61000-4-3	10V/m	perf. Criteria A
	EFT	IEC/EN 61000-4-4	±2KV	perf. Criteria A
Immunity	Surge	IEC/EN 61000-4-5	line to line ±2KV	perf. Criteria A
	CS	IEC/EN61000-4-6	10Vr.m.s	perf. Criteria A
	Voltage dips, short interruptions and voltage variations	IEC/EN61000-4-11	0%,70%	perf. Criteria A


Product Characteristic Curve




Note: ① With an AC input between 85-100VAC and a DC input between 120-140VDC, the output power must be derated as per temperature derating curves; ② This product is suitable for applications using natural air cooling; for applications in closed environment please consult factory or one of our FAE.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro







Dimensions and Recommended Layout



THIRD ANGLE PROJECTION





Pin-Out		
Pin	LI60-20B	
1	AC(L)	
2	AC(N)	
3	+Vo	
4	+Vo	
5	-Vo	
6	-Vo	

Note: Unit: mm[inch] ADJ: adjustable resistance to change output voltage Wire range: 24-12 AWG Tightening torque: Max 0.4 N·m Mounting rail: TS35 General tolerances: ±1.00[±0.039]

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

