

## Hinged-door cabinet with solid sheet metal doors, height 1950 mm

With shelves

### Application:

For secure and clearly-visible storage of tools, accessories, files or many other parts.

### Execution:

- Stable spot-welded steel sheet structure with base
- Safety bevelling to prevent injuries
- 2 reinforced hinged doors, mounted on 4 sturdy internal steel pins
- 4 galvanised shelves, can be adjusted in the grid by 50 mm
- Can be locked using three-point security levers and black turning knob with cylinder security lock, incl. 2 keys



<b>Art. no.</b>	<b>50045 010</b>
<b>Door design</b>	Full-sheet panel
<b>Width</b>	950 mm
<b>Depth</b>	450 mm
<b>Height</b>	1950 mm
<b>Number of shelves</b>	4 PCS
<b>Load-carrying capacity per shelf</b>	80 kg
<b>Load-carrying capacity</b>	300 kg
<b>With partition wall</b>	No
<b>Central locking</b>	Yes
<b>Lock type</b>	Twist-grip lock with three-point fastening
<b>Material</b>	Sheet steel
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Gentian blue RAL 5010
<b>Surface</b>	Lacquered
<b>Gross Weight</b>	68.000 kg
<b>Product Group</b>	586

### EAN

4250618202709