

Drawer cabinets

Mobile with a pair of roller carriers and nylon rollers Ø 100 mm



Application:

For day-to-day heavy-duty use in workshops

Execution:

- All drawers with full extension
- Individual drawer lock as standard feature to prevent the cabinet from tipping over
- Perforated, slotted drawers provide a secure hold
- Very robust construction for a wide variety of applications and very demanding requirements

Advantage:

- Optimum drawer surface height provides ideal protection against items falling out and becoming lost
- Folding handle strips for simple, clean and protected labelling
- High quality - made in Germany and Swiss-made
- Runs perfectly smoothly and easily due to the lack of crossbars on the differential extension slide
- Full extension - clear overview and optimal access

Delivery:

1 anti-roll-off edging, 4-sided, 1 sliding rod, 1 roller carrier pair with nylon rollers Ø 100 mm



Art. no.	50301 017
Brand	LISTA
Manufacturer Part Number	78.154.020
Number of drawers	5 PCS
Height	723 mm
Width	564 mm
Depth	725 mm
Height x width x depth	723 x 564 x 725 mm
Housing height	533 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	450 x 600 mm
Load-carrying capacity per drawer	75 kg
Drawer lock	Single lock right
Drawer front height	2 x 50 mm, 2 x 100 mm, 1 x 150 mm
Cabinet colour	Light grey RAL 7035
Colour of front	Light grey RAL 7035
Cabinet equipment	Pair of castors
With sliding handle	Yes
Height of roller carrier pair	137 mm
Wheel diameter	100 mm
Material of wheel	Nylon (polyamide)
Information about the direction	Along
Load-carrying capacity of roller	400 kg
Opening/closing system	Code Lock
Rim height	53 mm
Clear height	450 mm
LISTA unit	27 x 36 E
Gross Weight	98.000 kg
Product Group	5AN

EAN

7612269027501