

WE 17-125 Quick RT angle grinder

1750 watts

metabo®

Execution:

- maximum productivity through full performance with low weight
- perfect ergonomics thanks to slim grip area
- Metabo Marathon motor with new cooling and carbon brush system for twice the service life
- Metabo S-automatic mechanical safety coupling: minimises kickback from jammed discs to the lowest level on the market
- Tacho-Constamatic (TC) full-wave electronics: consistent rotation speed under load for good work progress
- gear unit housing can be fitted rotated in 90° steps
- cut-out carbon brushes protect the motor



Delivery:

includes protective hood, support flange, M-quick clamping nut, extra handle VibraTech, in box

Art. no.	70373 360
Brand	METABO
Manufacturer Part Number	601086000
Model	WE 17-125 Quick RT
Manufacturer Article Number	601086000
Battery included	No
Number of rechargeable batteries/batteries	0
Washer diameter	125 mm
Power input	1750 W
Power output	1070 W
Idle speed	11000 rpm
Thread dimension of spindle	M14
Weight	2.5 kg
With restart protection	Yes
With soft start	Yes
With overload protection	Yes
With electronic feedback	Yes
With reverse switch off	Yes
With disc brake	No
With quick clamping system	Yes
With dead man function	No
Max. torque	3.8 Nm
Cable length	4 m
Sound-pressure level	92 dB
Noise level	103 dB
Gross Weight	3.680 kg
Product Group	745

EAN

4007430311641

