

Pneumatic straight grinder G 551 D

MANNESMANN
DEMAG

Application:

Specially designed for fine milling, grinding, engraving and polishing work

Version:

- Ergonomic design
- Rear exhaust via hose unit with integrated silencer
- High speed for excellent machining quality

Advantage:

- High degree of concentricity for long run-times

Delivery:

Includes hose unit and collet chuck keys



Art. no.	75061 060
Valve design	Rotary valve
Max. idle speed	55000 rpm
Min./max. idle speed	0-55000 rpm
Power output	100 W
Air consumption	2 l/s
Sound-pressure level	74 dB
Length	120 mm
Diameter of housing	14 mm
Collet chuck diameter	3 mm
Suitable for max. sanding block diameter	8 mm
Max. HM rotating milling cutter diameter	6 mm
Weight	0.15 kg

EAN-Code

4251757300004