XP Power

1W

The CA Series is a high performance, precision regulated, high voltage converter with high stability and low ripple, along with a built-in voltage monitor output and an on-board precision voltage reference. Each model is programmed from 0 to 100% of rated output via a DAC compatible high impedance programming input. The voltage reference can be used to drive the high voltage output at 100% or to adjust the output with an external potentiometer or voltage divider. The output voltage monitor is internally buffered to provide a low impedance (up to 1mA) signal to external circuitry. A quasi-sinewave oscillator, internal transformer shielding, and an isolated steel case reduce EMI/RFI radiation to extremely low levels.

A proprietary encapsulation process and custom 94 V-0 listed, high performance formula are used to achieve excellent high voltage and thermal properties. CM Series Mounting Kits are available separately and can be used to convert any CA Series unit into a chassis mount solution with high voltage connectors.

Features

- 5V and 12V input models
- Precision voltage regulated
- Output voltages from 100V to 2000V
- 0 to 100% programmable output
- On-board voltage reference
- Operating temperature -10°C to +50°C
- <25ppm/°C temperature coefficient
- Shielded case with isolated case ground
- Ultra low ripple, down to 5ppm
- 3 year warranty

Block Diagram



DC-HVDC CONVERTER



Typical Applications



- Photo Multiplier Tube
- Solid State Detectors
- Avalanche Photodiodes
- Electrophoresis
- Piezo Devices
- Capacitor Charging
- EO Lenses

Dimensions

44.45 x 28.29 x 12.70mm (1.75" x 1.11" x 0.50")

POWERING THE WORLD'S CRITICAL SYSTEMS

Input

12Vin Models					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage, Vin	11.5	12.0	15.5	VDC	For 12Vin models
Input Current, No Load			80	mA	200V-1250V
Input Current, No Load			100	mA	2kV
Input Current, Full Load	0		220	mA	All Output Voltages
Programming Voltage, Vpgm			5	VDC	<150µA
510 A. A. A. A.					
5Vin Models					
5 Vin Models Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Characteristic	Minimum 4.75	Typical	Maximum 5.25	Units VDC	Notes & Conditions For 5Vin models
Characteristic Input Voltage, Vin Input Current, No Load	Minimum 4.75	Typical 5	Maximum 5.25 65	Units VDC mA	Notes & Conditions For 5Vin models 200V-1250V
Characteristic Input Voltage, Vin Input Current, No Load Input Current, No Load	Minimum 4.75	Typical 5	Maximum 5.25 65 155	Units VDC mA mA	Notes & Conditions For 5Vin models 200V-1250V 2kV
SVin Models Characteristic Input Voltage, Vin Input Current, No Load Input Current, No Load Input Current, Full Load	Minimum 4.75	Typical 5	Maximum 5.25 65 155 420	Units VDC mA mA mA	Notes & Conditions For 5Vin models 200V-1250V 2kV 200V-1250V
SVin Models Characteristic Input Voltage, Vin Input Current, No Load Input Current, No Load Input Current, Full Load Input Current, Full Load	Minimum 4.75	Typical 5	Maximum 5.25 65 155 420 550	Units VDC mA mA mA mA	Notes & Conditions For 5Vin models 200V-1250V 2kV 200V-1250V 2kV 200V-1250V

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage			2000	VDC	See Models & Ratings table
Output Current			10	mA	See Models & Ratings table
Output Programming	0		100	%	
Setpoint Accuracy ⁽⁴⁾		±1		%	
Gain Adjust ⁽⁵⁾		±1		%	Potentiometer
Linearity ⁽⁶⁾			±0.5	%	From 15% to 100% Vout
Minimum Load	No minimun	n load required			
Line Regulation	0.001		0.01	%	Conditions: 100% Vpgm, Full Load
Load Regulation	0.001		0.05	%	No Load to Full Load at 100% Vpgm, Nominal Vin
Short Circuit Protection	1			min	
Ripple and Noise	0.0005		0.01	%	1MHz bandwidth
Temperature Coefficient		25		ppm/°C	
Stability			50	ppm/hr	
Voltage Monitor Output	0		Max Vpgm	VDC	Range corresponds to 0 to 100% Vout
Voltage Reference Output		Max Vpgm			Vref is a fixed output equal to Max Vpgm

Notes:

1. Maximum rated output current is available from 100% Max Vout down to 50% Max Vout, then derates linearly from 50% Max Vout down to zero.

 Specifications after 1 hour warm-up, full load, 25°C unless otherwise indicated.
 Proper thermal management techniques are required to maintain safe case temperature.

4. SET POINT ACCURACY refers to the ability of the unit to accurately deliver the programmed voltage.

5. GAIN ADJUST refers to the ability to alter the gain of the circuit to allow for setpoint accuracy error.

6. LINEARITY refers to how much the transfer function can deviate from a straight line in the absence of any set-point error.



DC-HVDC CONVERTER

CA Series

General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Isolation	N/A - Input Ground is connected to Output Ground				
Switching Frequency	45		400	kHz	
Construction	Case material is zinc plated steel. Solid vacuum encapsulation, UL 94 V-0 rated				
Mean Time Between Failure	2.1			Mhrs	Per Bellcore TR 332 GB +25°C

Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Operating Temperature	-10		+50	°C	Case temperature	
Storage Temperature	-25		+95	°C		
Cooling	Natural convection					
Humidity			95	%RH	Non-condensing	
Thermal Shock Limit			1	°C/10sec		

Safety Approvals

Safety Agency	Standard	Notes & Conditions
UL	IEC/UL/EN62368	
CE	Meets all applicable directives	
RoHS	RoHS 2 and 3 Directive (2011/65/EU)	Where applicable

Notes:

1. Maximum rated output current is available from 100% Max Vout down to 50% Max Vout, then derates linearly from 50% Max Vout down to zero.

 Specifications after 1 hour warm-up, full load, 25°C unless otherwise indicated.
 Proper thermal management techniques are required to maintain safe case temperature.

4. SET POINT ACCURACY refers to the ability of the unit to accurately deliver the

programmed voltage.

5. GAIN ADJUST refers to the ability to alter the gain of the circuit to allow for setpoint accuracy error.

6. LINEARITY refers to how much the transfer function can deviate from a straight line in the absence of any set-point error.



Models & Ratings

Madel Number			Regu	lation	Disale	-	Input Voltage
Model Number	Output Voltage	Output Current ⁽¹⁾	Load	Line	кірріе	Frequency	
CA02N	0 to -200V	5mA	<0.05%	<0.01%	<0.01%	80-230kHz	12V
CA02N-5	0 to -200V	5mA	<0.005%	<0.003%	<0.01%	100-250kHz	5V
CA02P	0 to +200V	5mA	<0.05%	<0.01%	<0.01%	80-180kHz	12V
CA02P-5	0 to +200V	5mA	<0.01%	<0.01%	<0.01%	100-250kHz	5V
CA05N	0 to -500V	2mA	<0.01%	<0.01%	<0.01%	100-250kHz	12V
CA05N-5	0 to -500V	2mA	<0.005%	<0.002%	<0.005%	87-350kHz	5V
CA05P	0 to +500V	2mA	<0.01%	<0.01%	<0.01%	200-400kHz	12V
CA05P-5	0 to +500V	2mA	<0.003%	<0.002%	<0.005%	100-250kHz	5V
CA10N	0 to -1000V	1mA	<0.005%	<0.001%	<0.001%	100-250kHz	12V
CA10N-5	0 to -1000V	1mA	<0.005%	<0.001%	<0.001%	100-250kHz	5V
CA10P	0 to +1000V	1mA	<0.005%	<0.001%	<0.001%	80-250kHz	12V
CA10PR	0 to +1000V	1mA	<0.005%	<0.001%	<0.001%	80-250kHz	12V
CA10P-5	0 to +1000V	1mA	<0.005%	<0.001%	<0.001%	100-250kHz	5V
CA12N	0 to -1250V	0.8mA	<0.005%	<0.001%	<0.0005%	80-250kHz	12V
CA12N-5	0 to -1250V	0.8mA	<0.005%	<0.001%	<0.001%	150-300kHz	5V
CA12P	0 to +1250V	0.8mA	<0.005%	<0.001%	<0.0005%	80-250kHz	12V
CA12P-5	0 to +1250V	0.8mA	<0.005%	<0.001%	<0.001%	150-250kHz	5V
CA20N	0 to -2000V	0.5mA	<0.01%	<0.01%	<0.001%	100-250kHz	12V
CA20N-5	0 to -2000V	0.5mA	<0.001%	<0.001%	<0.001%	100-250kHz	5V
CA20P	0 to +2000V	0.5mA	<0.01%	<0.01%	<0.001%	80-250kHz	12V
CA20P-5	0 to +2000V	0.5mA	<0.005%	<0.003%	<0.001%	45-250kHz	5V

Notes:

Other voltages available on request - please contact our dedicated support team: xppower.com/contact



Mechanical Details



(1.300)

4.75 (0.187) MIN DIA FOR POT ACCESS 19.05 (0.750) 26.67 (1.050) 0 7 0 ¢ 5.59 6.35 € • (0.220) đ (0.250) 4 6 -³+ 8 19.05 (0.750) • 14.61 (0.575) 22.86 (0.900) 33.02 (1.300)⁻ RECOMMENDED HOLE AND PAD SIZE: Ø 1.32 (0.052) AND Ø 2.29 (0.090) 8 PLACES

Pin	Function	Description	5Vin	12Vin		
1	VOUT	High Voltage Output	Ground	to Pin 8		
2	VPGM	Voltage Programming Input, <150µA	0 to +2.048V	0 to +5V		
3	SGND	Signal Ground (for VPGM, VIN, VMON)	Low Voltag	Low Voltage Ground		
4	VREF	Voltage Reference Output, ±1%, 1mA	+2.048V	+5V		
5	CGND	Case Ground	Case (Case Ground		
6	VIN	Input Voltage	+4.75 to +5.25V	+11.5V to +15.5V		
7	VMON	Voltage Monitor Output, 1mA, scales to 0 to 100% Vout	0 to +2.048V	0 to +5V		
8	HV RTN	HV Output Return	Ground	for Pin 1		

Notes:

- 1. All dimensions are in mm (inches)
- 2. Weight: 39.6g (1.4oz)
- 3. Tolerance: X.XX±0.51 (0.02)

4. Pin Tolerance: ±0.127 (0.005)

5. All grounds internally connected except case. Case Ground (Pin 5) must be connected to ground, with no more than 50V between case ground (Pin 5) and circuit ground (Pin 3).

6. On negative output models, voltage monitor is buffered representation of programming voltage.



DC-HVDC CONVERTER

CA Series

Mounting Kit



Product Description

These adapters provide convenient prototyping and evaluation during system development and integration. They allow C Series modules to be mounted to a chassis instead of designed into a PC board. Extra filtering on the input and output improves performance. A schottky diode on the input provides reverse polarity protection. Input connector is via a 15P SUB MIN-D plug (mate supplied) and output is via an SHV style coaxial connector (mate supplied). Please note when ordering a CM3 the C Series is not included and must be ordered separately.

Programming Instructions

Onboard Potentiometer: connect pins 7 to 4 and 8 to 3, turn potentiometer to adjust high voltage. Or Remote Potentiometer: connect wiper arm to pin 3, other sides to pins 4 and 2. Or Remote Analog Signal: apply programming voltage to pin 3, return to pin 2.



Mounting Kit

CM2: SHV Connector



Product Description

These adapters provide convenient prototyping and evaluation during system development and integration. They allow C Series modules to be mounted to a chassis instead of designed into a PC board. Extra filtering on the input and output improves performance. A schottky diode on the input provides reverse polarity protection. Input connector is via a 15P SUB MIN-D plug (mate supplied) and output is via an SHV style coaxial connector (mate supplied). Please note when ordering a CM3 the C Series is not included and must be ordered separately

Programming Instructions

Onboard Potentiometer: connect pins 7 to 4 and 8 to 3, turn potentiometer to adjust high voltage. Or Remote Potentiometer: connect wiper arm to pin 3, other sides to pins 4 and 2. Or Remote Analog Signal: apply programming voltage to pin 3, return to pin 2.



Application Notes

Connection Diagram for VREF programming

For best performance a separate voltage source should be used for the voltage programming input. If this is not available, the user can utilize the voltage reference output (VREF), along with a user provided potentiometer, for the voltage programming input (VPGM).



Programming Voltage vs Output Voltage



Sequencing

For the CA Series, it is recommended to wait at least 100msec after input power is applied before sending a voltage programming command.

Dynamic Response

In cases where the output voltage rises above the voltage programming command then settles. To mitigate this effect, ramp the voltage programming input at a slower rate until satisfactory results are achieved.