

1393277-4 ✓ ACTIVE

TE Internal #: 1393277-4

TE Internal Description: V23076A1001C133

[View on TE.com >](#)



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought



TE Part #2-644861-7  
Polyester Vertical PCB Header: 2.54 mm, Shrouded, MTA 100



TE Part #2-1445084-2  
micro mnl hdr assy s/row au lf



TE Part #1969803-1  
03P UMNL PIN HDR ASSY NATL, PIN V0 GW



TE Part #2-2176156-0  
Metal Chip Resistor: Current Sense



TE Part #1624365-1  
NTC0805 5% 5K0



TE Part #1-1879223-3  
CPF 0603 316R 0.1% 25PPM 1K RL



TE Part #1379095-1  
COV+LEV MQS 12W 0DEG BROW



TE Part #1-1879023-6  
3650 1008 82nH 5% 2K RL



TE Part #2335893-1  
AMPLIMITE SZ 1 RECPT 15 POS, ST STL SHEL



TE Part #9-2176366-4  
RQ 0603 4K02 0.1% 10PPM 1K RL

## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1393277-4\\_O.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1393277-4\\_O.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1393277-4\\_O.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### Automotive Relay Application Notes

English

#### Power Relay K (Sealed), Single, PCB

English



---

**Product Specifications**

Definitions, Handling, Processing, Testing and Use of Relays

English