

Pneumatic turbine grinder TVD 3-100/2

80 watt



Application:

For the finest deburring work.

Execution:

- Exhaust air discharge to the front
- With elastic bearing

Advantage:

- Optimum surface quality thanks to high speed and elastic bearing
- Turbine motor - oil-free operation

Delivery:

Includes collet chuck ZG 5/3 mm, collet chuck key size 6 + 8 and hose unit; in box



Art. no.	75036 005
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150149906
Model	TVD 3-100/2
Valve design	Rotary valve
Motor design	Turbine motor
Max. idle speed	100000 rpm
Power output	80 W
Air consumption	180 l/min
Sound-pressure level	70 dB
Inner hose diameter	4.5 mm
Length	98 mm
Diameter of housing	31 mm
Max. clamping diameter	3 mm
Collet chuck diameter	3 mm
Suitable for max. sanding block diameter	5 mm
Max. HM rotating milling cutter diameter	3 mm
Weight	0.25 kg
Gross Weight	0.848 kg
Product Group	748