


IE5343



Inductive sensor

IEBC003BASKG



Product characteristics

Electrical design		PNP/NPN
Output function		normally open
Sensing range	[mm]	3
Housing		threaded type
Dimensions	[mm]	M8 x 1 / L = 37

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 10; (only in 3-wire operation)
Protection class		III
Reverse polarity protection		yes

Outputs

Electrical design		PNP/NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	2.8
Minimum load current	[mA]	2; (only in 2-wire operation)
Max. leakage current	[mA]	0.5; (only in 2-wire operation)
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	1000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Sensing range	[mm]	3
Operating distance	[mm]	0...2.4

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...15

Operating conditions

Ambient temperature	[°C]	0...70
Protection		IP 67



IE5343



Inductive sensor

IEBC003BASKG

Tests / approvals		
EMC		EN 60947-5-2
MTTF	[years]	3019
UL approval	Ta	-25...80 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	File number UL	E174191
Mechanical data		
Weight	[g]	51.5
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 37
Thread designation		M8 x 1
Materials		brass white bronze coated; sensing face: LCP
Tightening torque	[Nm]	A = 5 mm: 1,5 Nm; B: 2 Nm
Displays / operating elements		
Display		switching status 1 x LED, yellow
Accessories		
Accessories (supplied)		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.14 mm ²		
Connection		



Core colours :

- BK = black
- BN = brown
- BU = blue

IE5343

Inductive sensor

IEBC003BASKG



Diagrams and graphs

Installation

