

Dot laser, green, 520 nm, 5 mW

DD520-5-5(14x35)-QCW-DOE
Order Number: 70124217

Main Parameters (*)	min	typ	max	Unit
Wavelength	510	520	530	nm
Optical Output Power		5		mW
Operating Voltage	3	5	8	V DC
Operating Current	150	180	220	mA
Operating Temperature	-10		60	°C
Storage Temperature	-40		80	°C

Main Data

Warranty 1 years

Technical Parameters

Lifetime > 6,000 h
RoHS yes

Optical Parameters

Beam Shape	Dot
Laser Class	3R
Divergence	D - 0.5 mrad
Size of Laserdot	<8mm@10m
Operating Distance	20 m
Optics	glass lens AR coated
Laser technology	Single Mode Diode
Stability	+/- 3% @ -10-50°C
Focus	collimated
internal modulation frequency	1 kHz

Electrical Parameters

Potential of Housing isolated
Power Supply LFNT-5

Mechanical Parameters

Size	Ø14x35 mm
Material	aluminium
Cable length	100 mm
Wire type	26AWG, 0,14mm ²
Output Aperture	3 mm
Housing Color	black
Weight	16 g
PCB	no
Stripping of wire	5 mm

(*) Over the complete operating temperature range

Features



- For 8mm DOE
- Low Power consumption
- Direct green 520nm


Picture



Cable color

Ground  black GND
positive  red 3 - 8, typ 5 V DC

Safety Label



Valid Revision

| 08-MAR-2018