

Solid carbide end mill

3-cutter, uncoated

ORION[®]

Application:

Universal end mill for plunge, groove and slot milling as well as for face and circumferential milling.



Execution:

- Solid carbide ultra-fine grain
- Straight shank pursuant to DIN 6535 HA
- Up to Ø 3 mm - 3-cutter, cutting to the centre
- From Ø 3.5 mm - centre cutting

Art. no.	16780 020
Brand	ORION
Manufacturer Part Number	16780020
Cutting material	SC
Surface	Uncoated
Type	N
Number of cutting edges	3 PCS
Twist angle	30°
Tool holding device	HA parallel shank
Construction length	Normal
Cutting edge diameter	2 mm
Cutting edge length	6 mm
Length	38 mm
Shank diameter	3 mm
fz steel 1000	0.01 mm
Gross Weight	0.010 kg
Overall stainless steel suitability	1
fitness not iron total	2
fitness Titan/Nickel/Super total	2
Product Group	148

EAN

4039247108824