

Miniature cutting insert, type AG HC5615

For internal recessing

ATORN[®]



Application

For internal recessing in the material groups steel, stainless steel and special alloys, hard machining up to 65 HRC at high cutting speeds and under average cutting conditions.

Version

- Solid carbide cutting insert with internal cooling

Advantage

- Very hard cemented carbide grade ensures low wear
- Stable geometry for the cutting insert
- Innovative coating technology for universal use with very high service life requirements

Art. no.	17129 430
ISO name	AG
Shaft diameter	6 mm
Length	51 mm
Clearance length	15 mm
Programming size 2	1.4 mm
Recessing width	1.5 mm
Programming size	2.8 mm
Min. bore diameter	6.1 mm
Machining direction	Left
Carbide type	HC5615
Material to be processed	Steel, Stainless steel, Special alloy, Hardened material

EAN-Code

4050293377859