

SVQC steel boring bar, positive right
for longitudinal and copy turning using VC indexable inserts

ATORN®

Application

For longitudinal and copy turning with VC indexable insert 35°

Version

- Precision-made boring bar, **steel**, with internal cooling, type V, attack angle 107.5°, tip angle 35°, clearance angle 7°

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



| | |
|---------------------------------------|------------------|
| Art. No. | 17849 101 |
| ISO name | A16Q SVQC R/L 11 |
| Min. bore diameter | 21 mm |
| Shaft diameter | 16 mm |
| Clearance length | 16.5 mm |
| Length | 180 mm |
| Clamping surface height | 15 mm |
| Suitable for indexable inserts | VC.. 11.. |
| Tool design | Left |

EAN-Code

4050293562378