

## Swarf containers, tip from the forklift operator's seat

Carrying capacity up to 1500 kg, perforated metal plate over entire floor

### Application:


For the collection and separation of liquids from solids and for the transport or disposal of all types of waste, bulk materials, chips and mass-produced parts.

### Version:

- Perforated metal plate screwed across the entire base, 100 mm above the base, hole diameter 3 mm, spacing 6 mm
- Drain valve 1" for draining off liquids
- Tilting at any height using a wire rope from the stacker seat
- Sheet metal tray with surrounding edge profile
- Sturdy base frame with fork pockets
- Protection against accidental slipping and tipping

### Delivery:

Goods supplied without packaging as standard. Packaging available for an additional charge.



<b>Art. no.</b>	<b>50266 343</b>
<b>Volume</b>	1 m <sup>3</sup>
<b>Length</b>	1640 mm
<b>Width</b>	1280 mm
<b>Tipper edge height</b>	565 mm
<b>Height</b>	780 mm
<b>Fork pocket clearance</b>	495 mm
<b>Fork pocket size (W x H)</b>	200 x 60 mm
<b>With drain valve</b>	Yes
<b>With stacker seat tilt function</b>	Yes
<b>With perforated sheet</b>	Yes
<b>Load-carrying capacity</b>	1500 kg
<b>Surface</b>	Lacquered
<b>Colour</b>	Light blue RAL 5012

### EAN-Code

4052462025226