

## Sling swivels, hoist rings

CARTEC

### Application:

Attachment point for lifting loads.

### Execution:

- Suitable for secure raising of loads according to Machinery Directive
- 2006/42/EC
- constructed, tested and certified according to GS-OA 15-04 – EN 1677
- DGUV certification
- Magnaflux crack tested to 100%
- can be rotated 360°

### Advantage:

- load direction 90°, with minimal space requirement
- Durable corrosion protection of screw
- designed for a load of 20,000 load changes



<b>Art. no.</b>	<b>77239 121</b>
<b>Brand</b>	CARTEC
<b>Manufacturer Part Number</b>	C806XHT20
<b>Thread dimension</b>	M20
<b>Load-carrying capacity</b>	3.5 t
<b>External width</b>	87 mm
<b>Internal width</b>	55 mm
<b>Width of support plate</b>	45 mm
<b>Bracket diameter</b>	16 mm
<b>Usable thread length</b>	31 mm
<b>Bracket height</b>	111 mm
<b>Thread length</b>	31 mm
<b>Width across flats</b>	30 mm
<b>Distance between lower edge of retainer holder and retainer</b>	44 mm
<b>Gross Weight</b>	1.327 kg
<b>Product Group</b>	775

### EAN

8013429011894