

CERTIFICATE OF COMPLIANCE

Certificate Number 20190912-E216848
Report Reference E216848-20161220
Issue Date 2019-SEPTEMBER-12

Issued to: PFLITSCH GmbH & Co. KG
Ernst-Pflitsch-Strasse 1
42499 Hueckeswagen GERMANY

**This certificate confirms that
representative samples of**

OUTLET BUSHINGS AND FITTINGS
See Addendum Page For Models

Have been investigated by UL in accordance with the
Standard(s) indicated on this Certificate.

Standard(s) for Safety: UL 514B and CSA C22.2 NO. 18.3-12 Conduit, Tubing, and
Cable Fittings

Additional Information: See the UL Online Certifications Directory at
<https://iq.ulprospector.com> for additional information.

This *Certificate of Compliance* does not provide authorization to apply the UL Mark. Only the UL Follow-Up
Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's
Follow-Up Services.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Director North American Certification Program
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please
contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number 20190912-E216848
Report Reference E216848-20161220
Issue Date 2019-SEPTEMBER-12

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Liquid-Tight Flexible Cord Connectors, Cat. Nos. BLUE GLOBE – bgSS 220ms11- 7, 220bg220msAC11, 220bg220VAAC11, 220bg220msAC09, 220bg220VAAC09, 820bg220msAC11, 820bg220VAAC11, 820bg220msAC09, 820bg220VAAC09, 220bg220msAC13, 220bg220VAAC13, 820bg220msAC13, 820bg220VAAC13, 220bg225msAC15, 220bg225VAAC15, 820bg225msAC15, 820bg225VAAC15, bgSS225ms12-10, 225bg225msAC17, 225bg225VAAC17, 825bg225msAC17, 825bg225VAAC17, bgSS225ms16-12, bgSS232ms16-12, 232bg232msAC23, 232bg232VAAC23, 832bg232msAC23, 832bg232VAAC23, bgSS232ms20-16, 232bg240msAC27, 232bg240VAAC27, 832bg240msAC27, 832bg240VAAC27, 240bg240msAC31, 240bg240VAAC31, 840bg240msAC31, 840bg240VAAC31, 250bg250msAC36, 250bg250VAAC36, 850bg250msAC36, 850bg250VAAC36, 250bg250msAC40, 250bg250VAAC40, 850bg250msAC40, 850bg250VAAC40, 263bg263msAC46, 263bg263VAAC46, 863bg263msAC46, 863bg263VAAC46, 263bg263msAC51, 263bg263VAAC51, 863bg263msAC51, 863bg263VAAC51, bg 216VA 11/sc.

bg 216, bg 220, bg 225, bg 232, bg 240, bg 250, bg 263, bg 816, bg 820, bg 825, bg 832, bg 840, bg 850, bg 863, bg 24034. Followed by any combinations of the Suffixes described below:

Suffix – ms, VA, V4A, tri, VAtri, NM, triNM, V4AtriNM, V4Atri, VAtriNM, bgSS 220ms followed by 11-7, 12-10, 16-12, 20-16, VAAC11, VAAC13, VAAC15, AC11, AC13, AC15, etc.... , bgSS followed by 11-7, 12-10, 16-12, 20-16.

Suffix – PA, PAn and PAn-1(only for bg 220, bg 225, bg 232, bg 24034; not for bg 216, bg 816, bg 240, bg 840, bg 250, bg 850, bg 263 and bg 863 series).



Bruce Mahrenholz, Director North American Certification Program
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>

