

## Twist drill type H with soldered cemented carbide insert 4xD

For hard machining up to 63 HRC

**ORION**<sup>®</sup>

### Application:

Hard machining up to 63 HRC.

### Execution:

- Twist drill with universal standard geometry, soldered cemented carbide insert (K20) and driving lug on the clamp shank

### Advantage:

- Cemented carbide insert, K20, for a long service life
- polished chipping spaces ensure good chip removal
- long service life in hardened steel



<b>Art. no.</b>	<b>11162 060</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11162060
<b>Cutting edge diameter</b>	6 mm
<b>Chip flute length</b>	32 mm
<b>Length</b>	71 mm
<b>f hard 65 HRC</b>	0.06 mm/r
<b>DIN</b>	8037
<b>Gross Weight</b>	0.014 kg
<b>Product Group</b>	140

### EAN

4039247030248