

Micromar 40 EWR-L electronic micrometer

IP65, Multimar data output



Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- Carbide-tipped measuring faces
- RESET (resetting the display)
- ABS (display can be set to zero without losing the reference to the ORIGIN)
- mm/inch changeover
- LOCK function (keypad lock)
- HOLD (measured value storage)
- ORIGIN (measurement pre-setting)
- TOL (input of tolerances and warning limits)
- DATA (in connection with data connection cable)
- HOLD (measured value storage)

Advantage:

- Digit height 10 mm
- Non-rotating spindle
- QUICK DRIVE quick adjustment 5 mm/U

Delivery:

Operating instructions, battery, setting gauge (from a measuring range of 25–50 mm), travel case



Art. no.	31403 554
Brand	MAHR
Manufacturer Part Number	4157022
Display	Digital
Min./max. length measuring range	50-75 mm
Min./max. length measuring range in inches	2-3 in
Digit increment	0.001 mm
Measuring surface diameter	6.5 mm
Measuring arrangement	Standard
Material of measuring bolt	Carbide
IP protection class	IP 65
Data transmission type	MarConnect bidirektional
Spindle clamping	No
Digit height	10 mm
Functions	Reset (Zeroing the display), ABS function, With mm / inch switching, Origin (Dimension preset), Lock-function (Keyboard lock), TOL (Tolerance and warning limits input), Hold-function (AE lock), Data key on cable, Bi-directional data interface
Min./max. measurement force	5-10 N
Error limit	3 µm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
DIN	863
Bracket depth	45 mm
Measuring spindle increments	5 mm
Calibration Group	D, E
Gross Weight	1.098 kg
Product Group	305

EAN

4059192058548