

Product Specifications DT4x & DT2x Desktop Printer

Model	DT2x	DT4x	
Print Method	Direct Thermal		
Resolution	203 dpi (8 dot/mm)		
Print Speed	7IPS (177 mm/s)	7 IPS (177 mm/s)	
Print Width	2.12" (54 mm)	4.25" (108 mm)	
Print Length	Min. 0.16" (4 mm)**; Max. 68" (1727 mm)		
Memory	Flash	4 MB Flash (2 MB for user storage)	
	SDRAM	16 MB	
Sensor Type	Fixed transmissive sensor, central aligned Adjustable reflective sensor		
Media	Types	Continuous form, gap labels, black mark sensing, and punched hole; label length set by auto sensing or programming	
	Width	0.6" (15 mm) Min. - 2.36" (60 mm) Max.	1" (25.4 mm) Min. - 4.64" (118 mm) Max.
	Thickness	0.003" (0.06 mm) Min. - 0.008" (0.2 mm) Max.	0.0024" (0.06 mm) Min. - 0.008" (0.2 mm) Max.
	Label Roll Diameter	Max. 5" (127 mm)	
	Core Diameter	1", 1.5" (25.4 mm, 38.1 mm)	
Printer Language	EZPL, GEPL, GZPL auto switch		
Software	Label Design Software	QLabel-IV / GoLabel (for EZPL only)	
	Driver	Windows 2000, XP, Vista, 8, Windows Server 2003 & 2008	
	DLL	Windows 2000, XP and Vista	
Resident Fonts	Bitmap Fonts	6, 8, 10, 12, 14, 18, 24, 30, 16x26 and OCR A&B Bitmap fonts 90°, 180°, 270° rotatable, single characters 90°, 180°, 270° rotatable Bitmap fonts 8 times expandable in horizontal and vertical directions	
	Scalable Fonts	90°, 180°, 270° rotatable	
	Bitmap Fonts	90°, 180°, 270° rotatable, single characters 90°, 180°, 270° rotatable	
Download Fonts	Asian Fonts	90°, 180°, 270° rotatable and 8 times expandable in horizontal and vertical directions	
	Scalable Fonts	90°, 180°, 270° rotatable	
Barcodes	1-D Bar Codes	Code 39, Code 93, EAN 8 /13 (add on 2 & 5), UPC A/E (add on 2 & 5), 1 2 of 5 & 1 2 of 5 with Shipping Bearer Bars, Codabar, Code 128 (subset A, B, C), EAN 128, RPS 128, UCC 128, UCC/EAN-128 K-Mart, Random Weight, Post NET, ITF 14, China Postal Code, HIBC, MSI, Plessey, Telepen, FIM, GS1 DataBar	
	2-D Bar Codes	PDF417, Datamatrix code, MaxiCode, QR code, Micro PDF417, Micro QR code, Aztec code	
Code Pages	Codepage 437, 850, 851, 852, 855, 857, 860, 861, 862, 863, 865, 866, 869, 737 Windows 1250, 1251, 1252, 1253, 1254, 1255, 1257 Unicode (UTF8, UTF16)		
Graphics	Resident graphic file types are BMP and PCX, other graphic formats are downloadable from the software		
Interfaces	Serial port: RS-232(DB-9)		
	USB port IEEE 802.3 10/100 Base-Tx Ethernet port (RJ-45)		
Control Panel	One Tri-color LED: Power (Green, Orange and Red) Function Key: FEED		
Power	Auto Switching 100-240VAC, 50-60Hz		
Real Time Clock	Standard		
Environment	Operation Temperature	41°F to 104°F (5°C to 40°C)	
	Storage Temperature	-4°F to 122°F (-20°C to 50°C)	
Humidity	Operation	30-85%, non-condensing	
	Storage	10-90%, non-condensing	
Agency Approvals	CE (EMC), FCC Class A, CB, cUL, CCC		
Dimension	Length	8.58" (218 mm)	8.58" (218 mm)
	Height	6.77" (172 mm)	6.53" (166 mm)
	Width	3.94" (100 mm)	6.61" (168 mm)
Weight	2.65 lbs (1.2 Kg), excluding consumables		
Options & Accessories	Cutter Module		
	Label Dispenser		
	External label roll holder for 10" (250 mm) O.D. label rolls		
	External label rewinder		

* Specifications are subject to change without notice. All company and/or product names are trademarks and/or registered trademarks of their respective owners.
 ** Minimum print height specification compliance can be dependent on non-standard material variables such as label type, thickness, spacing, liner construction, etc.
 Godex is pleased to test non-standard materials for minimum height printing capability.

Godex Europe GmbH, Amzähäuschen 36, D-42929 Wermelskirchen, Geschäftsführer: Roy Theisen, Barry Stuart Rose,
 Handelsregister-Nr. HRB 50788, Amtsgericht Köln, Ust.-IdNr. DE813195023, Steuer-Nr. 230/5714/0190, WEEE Reg.-Nr. DE45355452.

www.godexintl.com

Barcodes Made Easy