



Figure similar

AS-INTERFACE MOUNTING PLATE K60 FOR COMPACT MODULE K60, MOUNT. ON RAIL FOR 2 RIBBON CABLE, AS-INTERFACE CABLE (YELLOW) AND AS-INTERFACE CABLE 24 V (BLACK)

General technical data:		
Type of device		accessories digital I/O modules for operation in the field, IP67 - K60
Design of the product		K60 mounting plate for standard rail mounting
Note		For the previous version of the 3RK1901-0CB00 standard rail mounting it is also possible to order the standard rail adapter as a spare part: 3RX1660-0B. This adapter is not required for the new 3RK1901-0CB01 version.
Note 1		additional seals are required only when the flat cables end in the module (3RK1 902-0AR00)
Connections/ Terminals:		
connection		insulation piercing method for AS-Interface flat cable
Connection system		insulation piercing method for AS-Interface flat cable
Mechanical data:		
Type of mounting		for standard rail mounting
Ambient conditions:		
ambient temperature	°C	-25 ... +85
degree of protection		IP67 with screw-mounted K60 compact module
Certificates/ approvals:		

General Product Approval

Shipping Approval



Shipping Approval

other



[Confirmation](#)

[Declaration of  
Conformity](#)

[Environmental  
Confirmations](#)

Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK19010CB01>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3RK19010CB01/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RK19010CB01&lang=en>



last modified:

15.01.2015