

Dot laser, green, 520 nm, 5 mW

DA520-5-3(12x60)-QCW
Order Number: 70118698

Main Parameters (*)	min	typ	max	Unit
Wavelength		520		nm
Optical Output Power		5		mW
Operating Voltage	2.7	3	3.3	V DC
Operating Current	15	50	70	mA
Operating Temperature	-10		60	°C
Storage Temperature	-40		80	°C

Main Data

Warranty 1 years

Technical Parameters

Lifetime > 6,000 h
RoHS yes

Optical Parameters

Beam Shape Dot
Laser Class 3R
Divergence A - 0.1 mrad
Size of Laserdot adjustable
Operating Distance 100 m
Optics glass lens AR coated
Laser technology Single Mode Diode
Focus adjustable
internal modulation frequency 1 kHz

Electrical Parameters

Potential of Housing isolated

Mechanical Parameters

Size Ø12x60 mm
Material aluminium
Cable length 100 mm
Wire type 26AWG, 0,14mm²
Output Aperture 5 mm
Housing Color black
Weight 13 g
Stripping of wire 5 mm

(*) Over the complete operating temperature range

Features



- Isolated housing
- Laser Class 3R
- Compact size
- Anti-reflex coating


Picture



Cable color

Ground  black GND
positive  red 2.7 - 3.3, typ 3 V DC

Safety Label



Valid Revision

| 22-MAY-2019