



Sample image







Datasheet

Article number: 70021527


Designation: KG125.T204/04.E

Description: Switch Global Disconnecter


IEC 60947-3 EN 60947-3, VDE 0660 Teil 107						
Rated insulation voltage Ui						
			Voltage (V) AC / DC			
			1000 AC			
Rated uninterrupted current Iu/Ith						
Current (A)	Ambient temperature (°C)		Peak temperature (°C) additional requirements			
125	50		55 Ambient temperature +50°C during 24 hours with peaks up to +55°C			
Rated operational current Ie						
Utilization category			Voltage (V)		Current (A)	
AC-32A			20 - 400		125	
Rated operational power						
Utilization category	Voltage (V)		No. of phases	No. of poles		Power (kW)
AC-3	220 - 240		3	3		22
AC-3	380 - 440		3	3		37
AC-3	660 - 690		3	3		30
AC-23A	220 - 240		3	3		30
AC-23A	380 - 440		3	3		45
AC-23A	660 - 690		3	3		37
Max Fuse Rating IEC						
Fuse characteristic			No. of Fuses		Current (A)	
gG			1		125	
UL60947-4-1, UL508						
Nominal Voltage						
			Voltage (V) AC / DC			
			600 AC			
Rated insulation voltage Ui						
			Voltage (V) AC / DC			
			600 AC			
Rated thermal current						
		Current (A)	Ambient temperature (°C)		Additional Text	
		150	0 - 40		ON-OFF switch (Valid when connected with wire rated for 75°C)	
		125	0 - 40		Change over switch (Valid when connected with wire rated for 75°C)	
Horsepower rating						
Across-the-Line Motor Starting			Voltage (V)	No. of phases	No. of poles	Power (HP)
DOL			110 - 120	1	2	7,50
DOL			220 - 240	1	2	20
DOL			277 - 277	1	2	20
DOL			440 - 480	1	2	35
DOL			550 - 600	1	2	35
DOL			110 - 120	3	3	15
DOL			220 - 240	3	3	30
DOL			440 - 480	3	3	60
DOL			550 - 600	3	3	60
SCCR / Max. fuse rating						
<i>Conditions of acceptability</i>						
This device is suitable for use on circuits capable of delivering not more than 10kA rms symmetrical amperes, 600V ac max. when protected by Type RK1 fuses.						
Suitable for use on a circuit capable of delivering not more than 65000 rms symmetrical amperes at 600V max., when protected by 300A Class J fuses.						
Temp. rating of wire						
			Temperature rating (°C)	Current (A) Text		
			75	-- --		
General Use						
AC / DC	Voltage (V)	Current (A)	No. of phases	No. of poles		No. of contacts in series
AC	277	125	1	1		1
AC	277	150	1	1		1
AC	600	150	1	2		1
AC	600	150	3	3		1
AC double-throw function	600	125	1	2		1
AC double-throw function	600	125	3	3		1

General Information						
<i>Text</i>						
- The operating handle and position indicating means to be used with these manual motor controllers should be provided from the manufacturer, or the operating handle and position indicating means to be used should have been previously evaluated in combination with the manual motor controllers.						
CSA						
Nominal Voltage						
				Voltage (V) AC / DC		
				600 AC		
Rated insulation voltage Ui						
				Voltage (V) AC / DC		
				600 AC		
Rated thermal current						
		Current (A)		Ambient temperature (°C)		Additional Text
		150		0 - 40		--
Horsepower rating						
<i>Across-the-Line Motor Starting</i>						
	Voltage (V)	No. of phases	No. of poles	Power (HP)	Ambient temperature [°C]	
DOL	110 - 120	1	2	7,50	40	
DOL	220 - 240	1	2	20	40	
DOL	277 - 277	1	2	20	40	
DOL	440 - 480	1	2	35	40	
DOL	550 - 600	1	2	35	40	
DOL	110 - 120	3	3	15	40	
DOL	220 - 240	3	3	30	40	
DOL	440 - 480	3	3	60	40	
DOL	550 - 600	3	3	60	40	
Temp. rating of wire						
			Temperature rating (°C)		Current (A) Text	
			75		-- --	
General Use						
AC / DC	Voltage (V)	Current (A)	No. of phases	No. of poles	No. of contacts in series	
AC	277	150	1	1	1	
AC	600	150	1	2	1	
AC	600	150	3	3	1	
GENERAL TECHNICAL INFORMATION						
Size of conductor						
<i>composition of conductor</i>	<i>Min. / Max. value</i>		<i>No. of conductor per terminal</i>	<i>Cross section (mm²) or (AWG/kcmil)</i>		<i>Material of the wire</i>
solid wire	Min.		1	6mm ²		Copper
flexible wire	Max.		1	70mm ²		Copper
flexible wire	Min.		1	16mm ²		Copper
flexible wire	Max.		1	AWG 2/0		Copper
Single-core or stranded wire	Max.		1	95mm ²		Copper
Single-core or stranded wire	Max.		1	AWG 3/0		Copper
flexible wire with sleeve	Max.		1	70mm ²		Copper
flexible wire with ferrule according to DIN 46228	Min.		1	10mm ²		Copper
Stripping length						
			Length (mm) --			
						
Recommended screw driver						
<i>Type of screw driver</i>			<i>Value</i>			
Hex key			5			
Tightening torque of screws						
			<i>tightening torque (Nm)</i>		<i>tightening torque (lb-in)</i>	
			14		125	
Approbations						
<i>Specification</i>						<i>Marking</i>
EAC						
CE marking						
UK Directives						
CSA C.22.2 No.14						
GB/T14048.3						
General Information						
<i>Text</i>						
- EMC Note: This device is suitable for use in environment A and B.						
- Do not lubricate or treat contacts.						
- Switches may only be mounted, connected and set into operation by qualified persons according to the accepted rules of technology.						
- Use copper wire only. Do not coat the wire end with tin.						
- Terminals with factory fitted jumper links are tightened during production. Take care during installation to ensure factory fitted links are not lost by undoing both sides of linked terminals. After wiring, all terminal screws must be tightened to recommended torque specifications.						

Waste Electrical & Electronic Equipment (WEEE)

Picture name	Description
	Do not throw in the trash as care must be taken to ensure environmentally sound disposal and recycling. Please either use an environmentally friendly waste disposal company; return to the supplier for disposal; or return direct to the manufacturer, Kraus & Naimer. You can find local Kraus & Naimer offices at www.krausnaimer.com

Proposition 65


Picture name	Description
	WARNING: This product can expose you to chemicals including nickel and lead, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov .

Classification Contact: Rigid contact bridge

Classification Contact Mat: Silver

Classification Terminal: Screw terminal


Mounting-E



IP - Code front side		IP66, IP67
Stages		1,00 - 12,00
A	□	68,00 mm
B	∅	6,00 mm
C	∅	13,00 - 17,00 mm
D	H	<= 5,50 mm
E	H	88,00 mm
G	H	8,50 mm
M	⌀	1,20 Nm
M1	⌀	1,50 Nm


Wiring diagram

KG125.T304.E



Face plate

S1.F456/E10.M1H



PADLOCK DEVICE

Designation: S2.V845/E11/A12

Face plate and handle unit: "E" face plate/yellow, frame/black, handle/red, locking push rod/yellow

Locking position: "1" at 270°+90° - knockouts every 45°

Angular displacement: "1" 1 x 90°

Type of mounting: "A" for type of mounting E

Type of version: "1" for same switch size

Switch type: "2" for KA-, KG- and KH(R)-switches

