

Machine tap extension with internal cooling and h6 shank

For the use of machine taps with internal cooling

ORION®

Application:

For extending machine taps in conjunction with deep and difficult to reach threads on CNC and conventional machines, in tapping chucks or quick-change chucks in single part production.



Execution:

- Steel tool holder with collet chuck and clamping nut h6 shank, steel shank of the extension pursuant to DIN for high requirements for process reliability and service life

Advantage:

- Very flexible and fast solution as there is no need to procure special machine taps
- User-friendly handling and short retooling times
- Excellent value for money

Art. no.	13533 521
Brand	ORION
Manufacturer Part Number	13533521
Suitable for DIN 374/376 screw tap	M18
Suitable for screw tap square socket size	11 mm
Size of square	11 mm
Collect depth	46 mm
Collet chuck diameter	14 mm
Collect outer diameter	22 mm
Shank diameter	14 mm
Length	330 mm
Shaft length	90 mm
Gross Weight	0.792 kg
Product Group	1DD

EAN

4053625475681