

## Collet type ER



### Application:

For drilling and centring tools.

### Execution:

- For NC lathes
- Burnished
- For suitable collets, see no. 23320
- No. 23308 008-020 ring profile key for tightening and loosening.

<b>Art. no.</b>	<b>22782 050</b>
<b>Brand</b>	EWS
<b>Manufacturer Part Number</b>	135944
<b>VDI mount diameter</b>	50 mm
<b>Collet type</b>	ER 40
<b>Min./max. clamping range</b>	3-26 mm
<b>Projecting length</b>	95 mm
<b>Outer diameter</b>	98 mm
<b>Gross Weight</b>	3.400 kg
<b>Product Group</b>	215

