



# MASTER PL-L 4 Pin

## MASTER PL-L 36W/830/4P 1CT/25

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	2G11 [ 2G11]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h
System Description	-
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	96 %
LSF 8000 h Rated	94 %
LSF 12000 h Rated	80 %
LSF Preheat 2000 h Rated	99 %

LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	98 %
LSF Preheat 8000 h Rated	97 %
LSF Preheat 16000 h Rated	82 %
LSF Preheat 20000 h Rated	50 %
Light Technical	
Color Code	830 [ CCT of 3000K]
Luminous Flux (Nom)	2900 lm
Luminous Flux (Rated) (Nom)	2900 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K

MASTER PL-L 4 Pin

Luminous Efficacy (rated) (Nom)	81 lm/W
Color Rendering Index (Nom)	>80
LLMF 2000 h Rated	94 %
LLMF 4000 h Rated	93 %
LLMF 6000 h Rated	92 %
LLMF 8000 h Rated	91 %
LLMF 12000 h Rated	90 %
LLMF 16000 h Rated	90 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Nom)	36 W
Lamp Current (Nom)	0.435 A

Temperature

Design Temperature (Nom)	30 °C
--------------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	4 Pins
----------------------	--------


Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	40 kWh

Product Data

Full product code	871150070674440
Order product name	MASTER PL-L 36W/830/4P 1CT/25
EAN/UPC - Product	8711500706744
Order code	927903408370
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927903408370
Net Weight (Piece)	104.000 g
ILCOS Code	FSD-36/30/1B-E-2G11

Dimensional drawing




PL-L 36W/830/4P

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 36W/830/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data

211

LDPB\_PLL4P\_830-Spectral power distribution B/W



LDPO\_PLL4P\_830-Spectral power distribution Colour

## MASTER PL-L 4 Pin

