

SPECIFICATION

Patent Pending

Part Number	:	FXP611.07.0092C
Product Name	:	"The Cloud" Flexible Polymer GPS/GLONASS/GALILEO/BeiDou Cloud Shape Antenna
Features	:	1559-1610 MHz 38mm*37mm*0.15mm size 92mm Cable IPEX MHFI Connector (U.FL compatible) RoHS Compliant





1. Introduction

This convenient "peel and stick" flexible polymer antenna is designed for applications which require high positioning accuracy using GPS, GLONASS, Galileo and even BeiDou functions on modern day GNSS systems. The antenna is designed to be mounted directly to plastic (e.g. ABS enclosure of a wireless device) and has been designed in a way that makes it extremely resistant to detuning affects caused by the device environment.



2. Specification

ELECTRICAL				
ANTENNA	GPS-GLONASS-GALILEO-BeiDou			
STANDARD				
Operation Frequency (MHz)	1559-1610			
Polarization	Linear			
Impedance (Ohms)	50			
Max VSWR	1.2:1			
Peak Gain (dBi)	3			
Efficiency (%)	80			
Average Gain (dB)	-1			
Radiation Properties	Omni- directional			
Max Input Power (Watts)	5			

* The FXP611 antenna performance was measured with 30X30 cm ABS Plastic.

MECHANICAL			
Antenna	GPS-GLONASS-GALILEO-BeiDou		
Standard			
Dimensions (mm)	38x37x0.15		
Required Space (mm)	40x40x0.2		
Material	Flexible Polymer		
Connector	MHFI(U.FL Compatible)		
Weight(g)	0.9		

** The FXP611 antenna requires at least 1cm clearance to metal or to the main device ground plane

ENVIRONMENTAL			
Antenna	GPS-GLONASS-GALILEO-BeiDou		
Standard			
Operation Temperature	-40°C to 85°C		
Storage Temperature	-40°C to 105°C		
Relative Humidity	40% to 95%		
RoHS Compliant	Yes		



3. Test Setup




Figure 1: Impedance, isolation and correlation coefficient measurements (left hand) and peak gain, average gain, efficiency and radiation pattern measurements (right hand)




4. Antenna Parameters

4.1. Return Loss


Return Loss 5 0 -5 -10 -15 -20 -25 -30 -35 -40 1550 1560 1570 1580 1600 1610 1620 1630 1640 1590 1650 MHz Figure 2: Return loss of FXP611 GPS/GLONASS/GALILEO/BeiDou Antenna

4.2. **VSWR**






4.3. Efficiency








4.4. Peak Gain

Figure 5: Peak Gain of FXP611 GPS/GLONASS/GALILEO/BeiDou Antenna




4.5. Average Gain





4.6. Radiation Pattern








Figure 8: Radiation Pattern of FXP611 GPS/GLONASS/GALILEO/BeiDou Antenna at 1575MHz






Figure 9: Radiation Pattern of FXP611 GPS/GLONASS/GALILEO/BeiDou Antenna at 1589MHz





Figure 10: Radiation Pattern of FXP611 GPS/GLONASS/GALILEO/BeiDou Antenna at 1610MHz




5. Mechanical Drawing





6. Packaging





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

© Taoglas