

[IMAGE]

Product Information

Product Category	REFRIGERATION
Unit Barcode	5016368092248
Outer Carton Barcode	
Commodity Code	8418103000
Country of Origin	CHINA
Primary Colour	WHITE
Finish	PAINTED STEEL
Primary Material	STAINLESS STEEL
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	NO

General Product Specification

Voltage	230
Frequency	50
Wattage	100
Rated Current	0.7
Fuse Rating	13
Plug Type	BS 1363
Cable Diameter	0.75
Cable Length	1.6
Class	CLASS I
Conformity Markings	CE+UKCA

Packaging & Shipping Information

Product Dimensions H x W x D (mm)	1440	480	505
Packaged Dimensions H x W x D (mm)			
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			36
Unit Packaged Weight (Kg)			
Carton Weight (Kg)			
EPS (Kg)	0.67	PPT Exempt Plastic (Kg)	0
Other Plastic (Kg)	0.58	Card / Paper (Kg)	2.28
Aluminium (Kg)	0	Steel (Kg)	0.012

Category Specific Technical Information

Type	OTHER REFRIGERATING APPLIANCE	Number of Freezer Compartments	3
Design Type	FREESTANDING	Number of Fridge Shelves	YES
Gross Total Volume		Door Hinge Position	
Net Total Volume	142	Reversible Door	WHITE
Net Refrigeration Volume	87	Door Handle Colour	ABS
Net Freezing Volume	55	Door Handle Material	METAL
Energy Efficiency Index	125	Door Material	135
Energy Rating	F	Door Opening Angle	FULL METAL
Airborne Acoustical Noise Emission Class		Housing Colour	1.5
Annual Energy Consumption	233	Lamp Rated Power	YES
Climate Class	N,ST	LED Lighting	420
Minimum Ambient Operating Temperature	16	Power Failure Safe Storage	
Maximum Ambient Operating Temperature	38	Temperature Rise Time	7
Winter Setting	NO	Thermostat Temperature Range	-22 TO 8
Freezer Star Rating	4	Thermostat Type	ELECTRONIC
Fast Freeze Facility	NO	Refrigerant Type	R600A
Freezing Capacity	2.5	Refrigerant Amount	53
Defrosting Type	M	RF: Back Panel Material	WHITE
Freezer Technology	STATIC		