

HUBER+SUHNER® DATA SHEET

Coaxial Cable Connector: 11_BNC-50-3-5/133_N



Description

Straight cable plug for flexible cable

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 4 GHz

Mechanical Data

Centre contact soldered
Outer contact clamped
Weight 0.0155 kg

Environmental Data

Operating Temperature -65 °C to 165 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Brass
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE
Coupling nut	Brass
Gasket	MVQ (Silicone Rubber)

Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00006654
Catalogue drawing	DOU-00006639
Assembly instruction	DOC-0000179064

Ordering Information

Single package 11_BNC-50-3-5/133_NE

Additional Information

Suitable cables RG_58_C/U, RG_223_U, ENVIROFLEX_142, RG 400 /U

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions