

COUPLING RELAY, AC-3, 15KW/400V, 1NO+1NC, DC 24V, W. PLUGGED-IN VARISTOR 3-POLE, SZ S0 SPRING-LOADED TERMINAL

| | | |
|---------------------|--|----------------|
| product brand name | | SIRIUS |
| Product designation | | Coupling relay |

General technical data:

| | | |
|---|----|------------|
| Insulation voltage | | |
| <ul style="list-style-type: none"> Rated value | V | 690 |
| Degree of pollution | | 3 |
| Surge voltage resistance Rated value | kV | 6 |
| Mechanical service life (switching cycles) | | |
| <ul style="list-style-type: none"> of the contactor typical | | 10 000 000 |
| <ul style="list-style-type: none"> of the contactor with added electronics-compatible auxiliary switch block typical | | 5 000 000 |
| <ul style="list-style-type: none"> of the contactor with added auxiliary switch block typical | | 10 000 000 |
| Thermal short-time current restricted to 10 s | A | 260 |
| Protection class IP | | |
| <ul style="list-style-type: none"> on the front | | IP20 |
| <ul style="list-style-type: none"> of the terminal | | IP20 |
| Equipment marking | | |
| <ul style="list-style-type: none"> acc. to DIN EN 61346-2 | | Q |
| <ul style="list-style-type: none"> acc. to DIN EN 81346-2 | | Q |

Main circuit:

| | | |
|---|--|---|
| Number of poles for main current circuit | | 3 |
| Number of NC contacts for main contacts | | 0 |
| Number of NO contacts for main contacts | | 3 |
| Operating voltage | | |

| | | |
|---|---|------|
| <ul style="list-style-type: none"> • at AC-3 Rated value maximum | V | 690 |
| Operating current | | |
| <ul style="list-style-type: none"> • at AC-1 <ul style="list-style-type: none"> — at 400 V at ambient temperature 40 °C Rated value — up to 690 V at ambient temperature 40 °C Rated value — up to 690 V at ambient temperature 60 °C Rated value • at AC-2 at 400 V Rated value • at AC-3 <ul style="list-style-type: none"> — at 400 V Rated value — at 500 V Rated value — at 690 V Rated value • at AC-4 at 400 V Rated value | A | 50 |
| | A | 50 |
| | A | 42 |
| | A | 32 |
| | A | 32 |
| | A | 21 |
| | A | 22 |
| Operating current with 1 current path | | |
| <ul style="list-style-type: none"> • at DC-1 <ul style="list-style-type: none"> — at 24 V Rated value — at 110 V Rated value — at 220 V Rated value — at 440 V Rated value — at 600 V Rated value • at DC-3 at DC-5 <ul style="list-style-type: none"> — at 24 V Rated value — at 110 V Rated value — at 220 V Rated value — at 440 V Rated value — at 600 V Rated value | A | 35 |
| | A | 4.5 |
| | A | 1 |
| | A | 0.4 |
| | A | 0.25 |
| | A | 20 |
| | A | 2.5 |
| | A | 1 |
| | A | 0.09 |
| | A | 0.06 |
| Operating current with 2 current paths in series | | |
| <ul style="list-style-type: none"> • at DC-1 <ul style="list-style-type: none"> — at 24 V Rated value — at 110 V Rated value — at 220 V Rated value — at 440 V Rated value — at 600 V Rated value • at DC-3 at DC-5 <ul style="list-style-type: none"> — at 110 V Rated value — at 220 V Rated value — at 24 V Rated value — at 440 V Rated value — at 600 V Rated value | A | 35 |
| | A | 35 |
| | A | 5 |
| | A | 1 |
| | A | 0.8 |
| | A | 15 |
| | A | 3 |
| | A | 35 |
| | A | 0.27 |
| | A | 0.16 |
| Operating current with 3 current paths in series | | |

| | | |
|--|-----|------|
| <ul style="list-style-type: none"> • at DC-1 <ul style="list-style-type: none"> — at 24 V Rated value — at 110 V Rated value — at 220 V Rated value — at 440 V Rated value — at 600 V Rated value • at DC-3 at DC-5 <ul style="list-style-type: none"> — at 110 V Rated value — at 220 V Rated value — at 24 V Rated value — at 440 V Rated value — at 600 V Rated value | A | 35 |
| | A | 35 |
| | A | 35 |
| | A | 2.9 |
| | A | 1.4 |
| | A | 35 |
| | A | 10 |
| | A | 35 |
| | A | 0.6 |
| | A | 0.6 |
| Operating power | | |
| <ul style="list-style-type: none"> • at AC-1 at 400 V Rated value • at AC-2 at 400 V Rated value • at AC-4 at 400 V Rated value | kW | 28 |
| | kW | 15 |
| | kW | 11 |
| Operating power | | |
| <ul style="list-style-type: none"> • at AC-1 <ul style="list-style-type: none"> — at 230 V at 60 °C Rated value — at 230 V Rated value — at 400 V at 60 °C Rated value — at 690 V at 60 °C Rated value — at 690 V Rated value • at AC-3 <ul style="list-style-type: none"> — at 230 V Rated value — at 400 V Rated value — at 690 V Rated value | kW | 15.5 |
| | kW | 16 |
| | kW | 27.5 |
| | kW | 47.5 |
| | kW | 48 |
| | kW | 7.5 |
| | kW | 15 |
| | kW | 18.5 |
| Operating power for ≥ 200000 operating cycles at AC-4 | | |
| <ul style="list-style-type: none"> • at 400 V Rated value • at 690 V Rated value | kW | 6 |
| | kW | 10.3 |
| Operating frequency | | |
| <ul style="list-style-type: none"> • at AC-3 maximum | 1/h | 750 |

Control circuit/ Control:

| | | |
|--|---|---------------|
| Type of voltage of the control supply voltage | | DC |
| Control supply voltage for DC | | |
| <ul style="list-style-type: none"> • Rated value | V | 24 |
| Operating range factor control supply voltage rated value of the magnet coil for DC | | 0.7 ... 1.25 |
| Design of the surge suppressor | | with varistor |
| Closing power of the magnet coil for DC | W | 4.5 |
| Holding power of the magnet coil for DC | W | 4.5 |

Auxiliary circuit:

| | | |
|---|----------------------------|---|
| Number of NC contacts | | |
| <ul style="list-style-type: none"> • for auxiliary contacts — instantaneous contact | | 1 |
| Number of NO contacts | | |
| <ul style="list-style-type: none"> • for auxiliary contacts — instantaneous contact | | 1 |
| Product expansion Auxiliary switch | | No |
| Operating current at AC-15 | | |
| <ul style="list-style-type: none"> • at 230 V Rated value • at 400 V Rated value • at 690 V Rated value | A A A | 10 3 1 |
| Operating current | | |
| <ul style="list-style-type: none"> • at DC-12 at 125 V Rated value • at DC-12 at 220 V Rated value • at DC-12 at 600 V Rated value • at DC-13 at 125 V Rated value • at DC-13 at 220 V Rated value • at DC-13 at 600 V Rated value | A A A A A A | 2 1 0.15 0.9 0.3 0.1 |
| Operating current | | |
| <ul style="list-style-type: none"> • at DC-12 <ul style="list-style-type: none"> — at 60 V Rated value — at 110 V Rated value • at DC-13 <ul style="list-style-type: none"> — at 24 V Rated value — at 60 V Rated value — at 110 V Rated value | A A A A A | 6 3 10 2 1 |
| Contact reliability of the auxiliary contacts | | 1 faulty switching per 100 million (17 V, 1 mA) |

UL/CSA ratings:

| | | |
|--|--|--------------------|
| Full-load current (FLA) for three-phase AC motor | | |
| <ul style="list-style-type: none"> • at 480 V Rated value • at 600 V Rated value | A A | 27 27 |
| yielded mechanical performance [hp] | | |
| <ul style="list-style-type: none"> • for single-phase AC motor at 110/120 V Rated value • for single-phase AC motor at 230 V Rated value • for three-phase AC motor at 200/208 V Rated value • for three-phase AC motor at 220/230 V Rated value | metric hp metric hp metric hp metric hp | 2 5 10 10 |

| | | |
|---|-----------|-------------|
| <ul style="list-style-type: none"> • for three-phase AC motor at 460/480 V Rated value | metric hp | 20 |
| <ul style="list-style-type: none"> • for three-phase AC motor at 575/600 V Rated value | metric hp | 25 |
| Contact rating of the auxiliary contacts acc. to UL | | A600 / Q600 |

Short-circuit:

| | | |
|---|--|---|
| Design of the fuse link | | |
| <ul style="list-style-type: none"> • for short-circuit protection of the main circuit <ul style="list-style-type: none"> — with type of assignment 1 required — with type of assignment 2 required • for short-circuit protection of the auxiliary switch required | | gL/gG LV HRC 3NA, DIAZED 5SB, NEOZED 5SE: 100 A gL/gG LV HRC 3NA, DIAZED 5SB, NEOZED 5SE: 35 A fuse gL/gG: 10 A |

Installation/ mounting/ dimensions:

| | | |
|---|----|--|
| mounting position | | +/-180° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface |
| Mounting type | | screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 50022 |
| <ul style="list-style-type: none"> • Side-by-side mounting | | Yes |
| Height | mm | 102 |
| Width | mm | 45 |
| Depth | mm | 107 |
| Required spacing | | |
| <ul style="list-style-type: none"> • with side-by-side mounting <ul style="list-style-type: none"> — forwards — Backwards — upwards — downwards — at the side • for grounded parts <ul style="list-style-type: none"> — forwards — Backwards — upwards — at the side — downwards • for live parts <ul style="list-style-type: none"> — forwards — Backwards — upwards — downwards | mm | 0 0 0 0 0 0 0 0 6 0 0 0 0 0 |

— at the side

mm 6

Connections/ Terminals:

| | | |
|--|--|-----------------------------------|
| Type of electrical connection | | |
| • for main current circuit | | spring-loaded terminals |
| • for auxiliary and control current circuit | | spring-loaded terminals |
| Type of connectable conductor cross-section | | |
| • for main contacts | | |
| — single or multi-stranded | | 2x (1 ... 10 mm ²) |
| — finely stranded with core end processing | | 2x (1 ... 6 mm ²) |
| — finely stranded without core end processing | | 2x (1 ... 6 mm ²) |
| • for AWG conductors for main contacts | | 2x (18 ... 8) |
| • for auxiliary contacts | | |
| — single or multi-stranded | | 2x (0,5 ... 2,5 mm ²) |
| — finely stranded with core end processing | | 2x (0.5 ... 1.5 mm ²) |
| — finely stranded without core end processing | | 2x (0.5 ... 2.5 mm ²) |
| • for AWG conductors for auxiliary contacts | | 2x (20 ... 14) |

Safety related data:

| | | |
|---|-----|-------------|
| B10 value with high demand rate acc. to SN 31920 | | 1 000 000 |
| Proportion of dangerous failures | | |
| • with low demand rate acc. to SN 31920 | % | 40 |
| • with high demand rate acc. to SN 31920 | % | 73 |
| Failure rate [FIT] with low demand rate acc. to SN 31920 | FIT | 100 |
| Product function Mirror contact acc. to IEC 60947-4-1 | | Yes |
| T1 value for proof test interval or service life acc. to IEC 61508 | y | 20 |
| Protection against electrical shock | | finger-safe |

Mechanical data:

| | | |
|--------------------------|--|----|
| Size of contactor | | S0 |
|--------------------------|--|----|

Ambient conditions:

| | | |
|--|----|---|
| Installation altitude at height above sea level maximum | m | 2 000 |
| Ambient temperature | | |
| • during operation | °C | -25 ... +60 |
| • during operation Note | | Railway application: -40 ... 70 °C with 10 mm clearance. See catalog for other rated conditions |
| • during storage | °C | -55 ... +80 |

Certificates/ approvals:

| | | |
|--------------------------|-----|---------------------------------------|
| General Product Approval | EMC | Functional Safety/Safety of Machinery |
|--------------------------|-----|---------------------------------------|



[Type Examination](#)

| | | |
|---------------------------|-------------------|-------------------|
| Declaration of Conformity | Test Certificates | Shipping Approval |
|---------------------------|-------------------|-------------------|



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

[other](#)



Shipping Approval



other

[Environmental Confirmations](#)

[Confirmation](#)



Further information



Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/industrial-controls/catalogs>


Industry Mall (Online ordering system)
<http://www.siemens.com/industrymall>

Cax online generator
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT20272KB40>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<http://support.automation.siemens.com/WW/view/en/3RT20272KB40/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT20272KB40&lang=en





last modified:

11.03.2015