

Printing date 30.04.2015 Version number 8 Revision: 29.04.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- · 1.1 Product identifier
- · Trade name: ST2100
- · 1.2 Relevant identified uses of the substance or mixture and uses advised against

No further relevant information available.

- · Application of the substance / the mixture Industrial marker
- · 1.3 Details of the supplier of the safety data sheet
- · Manufacturer/Supplier:

LA-CO INDUSTRIES EUROPE

Allée des Combes, PI de la Plaine de l'Ain

F-01150 BLYES

FRANCE

info@eu.laco.com

- · Further information obtainable from: Département sécurité du produit
- · 1.4 Emergency telephone number:
- BG: National Clinical Toxicology Centre, Tel.: +359 2 9154 409
- DK: Giftlingen Bispebjerg Hospital, Tel.: +45 82 12 12 12
- EE: Mürgistusteabekeskus, Tel.: +372 626 93 90
- FI: Myrkytystietokeskus, Tel.: +358 9 471 977
- GR: Poisons Information Centre, Tel.: +30 10 779 37777
- HR: Poisons Control Centre, Tel.: +385 1 234 8342
- HU: Orszagos Kemiai Biztonsagi Intézet, Tel.: +36 80 20 11 99
- IE: National Poisons Information Centre, Tel.: +353 1 809 2166
- LT: Apsinuodijimu kontrolès ir informacijos biuras, Tel.: +370 5 236 20 52
- LV: Valsts Toksikologijas centra, Tel.: +371 67 04 24 73
- RO: Biroul pentru Regulamentul Sanitar International si Informare Toxicologica, Tel.: +40 21 318 36 06
- SE: Swedish Poisons Information Centre, Tel.: +46 8 33 12 31
- SI: Poison Centre, Tel.: +386 41 650 500

SECTION 2: Hazards identification

- · 2.1 Classification of the substance or mixture
- · Classification according to Regulation (EC) No 1272/2008



GHS02 flame

Flam. Liq. 3 H226 Flammable liquid and vapour.



STOT SE 3 H336 May cause drowsiness or dizziness.

· Classification according to Directive 67/548/EEC or Directive 1999/45/EC

R10-67: Flammable. Vapours may cause drowsiness and dizziness.

· Information concerning particular hazards for human and environment:

The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

· Classification system:

The classification is according to the latest editions of the EU-lists, and extended by company and literature data.

- · 2.2 Label elements
- · Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

(Contd. on page 2)

(Contd. of page 1)



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 30.04.2015 Version number 8 Revision: 29.04.2015

Trade name: ST2100

· Hazard pictograms





GHS02 GHS07

- · Signal word Warning
- · Hazard-determining components of labelling:

n-butyl acetate

· Hazard statements

H226 Flammable liquid and vapour.

H336 May cause drowsiness or dizziness.

· Precautionary statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P241 Use explosion-proof electrical/ventilating/lighting/equipment.

P261 Avoid breathing dust/fume/gas/mist/vapours/spray.

P303+P361+P353 IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin

with water/shower.

P405 Store locked up.

P501 Dispose of contents/container in accordance with local/regional/national/international

regulations.

- · Labelling of packages where the contents do not exceed 125 ml
- · Hazard pictograms





GHS02

- · Signal word Warning
- · Hazard-determining components of labelling:

n-butyl acetate

- · Hazard statements Void
- · 2.3 Other hazards
- · Results of PBT and vPvB assessment
- · **PBT**: Not applicable.
- · vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

- · 3.2 Chemical characterisation: Mixtures
- **Description:** Mixture of substances listed below with nonhazardous additions.

· Dangerous components:

· Additional information: For the wording of the listed risk phrases refer to section 16.

SECTION 4: First aid measures

- · 4.1 Description of first aid measures
- · After inhalation: Supply fresh air; consult doctor in case of complaints.
- · After skin contact: Generally the product does not irritate the skin.
- · After eye contact: Rinse opened eye for several minutes under running water.
- · After swallowing: If symptoms persist consult doctor.

(Contd. on page 3)



Printing date 30.04.2015 Version number 8 Revision: 29.04.2015

Trade name: ST2100

(Contd. of page 2)

- · 4.2 Most important symptoms and effects, both acute and delayed No further relevant information available.
- $\cdot \textit{4.3 Indication of any immediate medical attention and special treatment needed}$

No further relevant information available.

SECTION 5: Firefighting measures

- · 5.1 Extinguishing media
- · Suitable extinguishing agents: CO2, sand, extinguishing powder. Do not use water.
- · For safety reasons unsuitable extinguishing agents: Water with full jet
- 5.2 Special hazards arising from the substance or mixture No further relevant information available.
- · 5.3 Advice for firefighters
- · Protective equipment: No special measures required.

SECTION 6: Accidental release measures

· 6.1 Personal precautions, protective equipment and emergency procedures

Wear protective equipment. Keep unprotected persons away.

· 6.2 Environmental precautions:

Do not allow product to reach sewage system or any water course.

Inform respective authorities in case of seepage into water course or sewage system.

Do not allow to enter sewers/ surface or ground water.

· 6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Do not flush with water or aqueous cleansing agents

· 6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

- 7.1 Precautions for safe handling No special precautions are necessary if used correctly.
- · Information about fire and explosion protection:

Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

- · 7.2 Conditions for safe storage, including any incompatibilities
- · Storage:
- Requirements to be met by storerooms and receptacles: No special requirements.
- · Information about storage in one common storage facility: Not required.
- · Further information about storage conditions: Keep container tightly sealed.
- · 7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

- · Additional information about design of technical facilities: No further data; see item 7.
- · 8.1 Control parameters
- · Ingredients with limit values that require monitoring at the workplace:

123-86-4 n-butyl acetate

WEL Short-term value: 966 mg/m³, 200 ppm Long-term value: 724 mg/m³, 150 ppm

· Additional information: The lists valid during the making were used as basis.

(Contd. on page 4)



Printing date 30.04.2015 Version number 8 Revision: 29.04.2015

Trade name: ST2100

(Contd. of page 3)

- · 8.2 Exposure controls
- · Personal protective equipment:
- · General protective and hygienic measures: Wash hands before breaks and at the end of work.
- · Respiratory protection: Not required.
- · Protection of hands:

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· Eye protection:



Tightly sealed goggles

SECTION 9: Physical and chemical properties

 9.1 Information on basic physical a General Information 	ina cnemicai properties	
· Appearance:		
Form:	Fluid	
Colour:	According to product specification	
· Odour:	Characteristic	
· Odour threshold:	Not determined.	
· pH-value:	Not determined.	
· Change in condition		
Melting point/Melting range:	Undetermined.	
Boiling point/Boiling range:	124 °C	
· Flash point:	27 °C	
· Flammability (solid, gaseous):	Not applicable.	
· Ignition temperature:	<i>370 ℃</i>	
· Decomposition temperature:	Not determined.	
· Self-igniting:	Product is not selfigniting.	
· Danger of explosion:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.	
· Explosion limits:		
Lower:	1.2 Vol %	
Upper:	7.5 Vol %	
· Vapour pressure at 20 °C:	10.7 hPa	
· Density:	Not determined.	
Relative density	Not determined.	

(Contd. on page 5)



Printing date 30.04.2015 Version number 8 Revision: 29.04.2015

Trade name: ST2100

		(Contd. of page 4
Vapour density	Not determined.	
Evaporation rate	Not determined.	
Solubility in / Miscibility with		
water:	Not miscible or difficult to mix.	
Partition coefficient (n-octanol/we	uter): Not determined.	
Viscosity:		
Dynamic:	Not determined.	
Kinematic at 20 °C:	300 s (ISO 6 mm)	
Solvent content:		
Organic solvents:	37.8 %	
VOC (EC)	37.77 %	
Solids content:	41.1 %	
9.2 Other information	No further relevant information available.	

SECTION 10: Stability and reactivity

- · 10.1 Reactivity
- · 10.2 Chemical stability
- · Thermal decomposition / conditions to be avoided: No decomposition if used according to specifications.
- · 10.3 Possibility of hazardous reactions No dangerous reactions known.
- · 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- · 10.6 Hazardous decomposition products: No dangerous decomposition products known.

SECTION 11: Toxicological information

- · 11.1 Information on toxicological effects
- · Acute toxicity:
- · Primary irritant effect:
- · on the skin: No irritant effect.
- · on the eye: No irritating effect.
- · Sensitisation: No sensitising effects known.

SECTION 12: Ecological information

- · 12.1 Toxicity
- · Aquatic toxicity: No further relevant information available.
- · 12.2 Persistence and degradability No further relevant information available.
- · 12.3 Bioaccumulative potential No further relevant information available.
- · 12.4 Mobility in soil No further relevant information available.
- · Additional ecological information:
- · General notes:

Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water

Do not allow product to reach ground water, water course or sewage system.

Danger to drinking water if even small quantities leak into the ground.

- · 12.5 Results of PBT and vPvB assessment
- · **PBT**: Not applicable.
- · vPvB: Not applicable.
- $\cdot \textbf{12.6 Other adverse effects} \ \textit{No further relevant information available}.$



Printing date 30.04.2015 Version number 8 Revision: 29.04.2015

Trade name: ST2100

(Contd. of page 5)

SECTION 13: Disposal considerations

- · 13.1 Waste treatment methods
- · Recommendation

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

- · Uncleaned packaging:
- · Recommendation: Disposal must be made according to official regulations.

SECTION 14: Transport information

· 14.1 UN-Number	
· ADR, ADN, IMDG	not regulated
· IATA	UN1263

· 14.2 UN proper shipping name

· ADR, ADN, IMDG not regulated · IATA PAINT

· 14.3 Transport hazard class(es)

· ADR, ADN, IMDG

· Class not regulated

 \cdot IATA



ClassLabel3 Flammable liquids.3

· 14.4 Packing group

· ADR, IMDG not regulated

· IATA

· 14.5 Environmental hazards:

· Marine pollutant: No

· 14.6 Special precautions for user Not applicable.

· 14.7 Transport in bulk according to Annex II of

MARPOL73/78 and the IBC Code Not applicable.

· UN "Model Regulation":

SECTION 15: Regulatory information

- · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture No further relevant information available.
- · 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H226 Flammable liquid and vapour.

(Contd. on page 7)



Printing date 30.04.2015 Version number 8 Revision: 29.04.2015

Trade name: ST2100

(Contd. of page 6)

H336 May cause drowsiness or dizziness.

R10 Flammable.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.

· Department issuing MSDS: Service protection de l'environnement

· Contact: Responsable QHSE

· Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International

Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU) Flam. Liq. 3: Flammable liquids, Hazard Category 3

STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3

GB