

# PANEL MOUNT INDICATOR, NON-RELAMPABLE

## NEON TECHNOLOGY

MOUNTING HOLE, Ø 0.500"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
<b>NEON 115VAC SERIES</b>				
WL-1060D1	RED	105-125VAC	1.5mA	25,000
WL-1060D3	AMBER	105-125VAC	1.5mA	25,000
WL-1060D4	WHITE	105-125VAC	1.5mA	25,000
WL-1060D5	GREEN	105-125VAC	1.5mA	25,000
<b>NEON 230VAC SERIES</b>				
WL-1061D1	RED	208-250VAC	1.5mA	25,000
WL-1061D3	AMBER	208-250VAC	1.5mA	25,000
WL-1061D4	WHITE	208-250VAC	1.5mA	25,000
WL-1061D5	GREEN	208-250VAC	1.5mA	25,000
<b>NEON 480VAC SERIES</b>				
WL-1062D1	RED	432-528VAC	1.5mA	25,000
WL-1062D3	AMBER	432-528VAC	1.5mA	25,000
WL-1062D4	WHITE	432-528VAC	1.5mA	25,000
WL-1062D5	GREEN	432-528VAC	1.5mA	25,000
<b>NEON 600VAC SERIES</b>				
WL-1063D1	RED	540-660VAC	1.5mA	25,000
WL-1063D3	AMBER	540-660VAC	1.5mA	25,000
WL-1063D4	WHITE	540-660VAC	1.5mA	25,000
WL-1063D5	GREEN	540-660VAC	1.5mA	25,000

## NOTES


1. Recommended panel thickness  
0.030" to 0.090"
2. 6" leads with 1/2" strip are standard
3. Storage temperature  
 $T_{STG}$ : -25°C - +80°C
4. Ambient temperature  
 $T_A$ : -20°C - +60°C
5. Voltage tolerance  
 $V_{OP}$ : ±10%
6. Body material  
Polycarbonate, white
7. Lens material  
Polycarbonate
8. Bezel material  
Stainless steel
9. Wire gauge  
20 AWG
10. Wire strip  
1/2"

## CERTIFICATIONS

UL (E340667), RoHS



## DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



## OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.



P: (714) 545-5560 F: (714) 545-6093

W: WWW.WAMCOINC.COM E: INFO@WAMCOINC.COM

WL-106xDx Series Rev 2