

Precision pointer snap gauges

Marameter



Application:


For precise testing of cylindrical parts in series.

Version:

- Carbide measuring faces
- Spring-mounted anvil
- Consistent, repeatable measuring force
- Forged steel bracket
- Measuring and counter probe made from stainless, hardened steel
- Adjustable centring stop

Delivery:

In wooden box, display unit not included



Art. no.	31936 100
Min./max. length measuring range	100-150 mm
Measuring surface diameter	12 mm
Measurement force	7.5 N
Shaft diameter	8 mm
Spindle clamping	Yes

EAN-Code

4059192017620