

Hinged-door cabinet with shelf and drawers

Doors with slotted panels

[®]RasterPlan

Application:

For clearly-arranged and space-saving storage of tools.

Version:

- Welded sheet steel structure with rear wall, ¼ slotted/¼ perforated panel for attaching support elements
- Overlay, double-walled, twist-resistant hinged doors, opening angle over 200°
- Three-point security cylinder lock with recessed turning handle



Art. no.	50639 257
Door design	Slotted plates
Width	1000 mm
Depth	600 mm
Height	1950 mm
Number of shelves	2 PCS
Shelf width	1000 mm
Shelf depth	600 mm
Load-carrying capacity per shelf	80 kg
Number of drawers	4 PCS
Drawer front height	4 x 100 mm
With worktop	No
Load-carrying capacity per drawer	110 kg
Pullout type	Full extension
With partition wall	No
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Colour of front	Anthracite grey RAL 7016
Surface	Lacquered
Cabinet colour	Light grey RAL 7035

EAN-Code

4251142238028