

SCLC clamp holder positive, left-hand

For face and longitudinal turning with CC indexable insert

ATORN[®]

Application

For face and longitudinal turning with CC indexable insert 80°

Version

- Precision-made steel carrier, burnished, hardened, type C, attack angle 95°, tip angle 80°, clearance angle 7°

Advantage

- Universal use for face and longitudinal turning
- Positive body geometry ensures low cutting forces
- Very good surfaces, for medium and finishing infeed



Art. no.	17830 097
ISO name	SCLC R/L 2525 M12
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Length of head	20 mm
Programming size	32 mm
Suitable for indexable inserts	CC.. 1204..
Tool design	Left
DIN	4983

EAN-Code

4050293566192