

## Flat-bed hand truck with wire grid walls

### Execution:

- Modular system
- From welded profile steel, 4 tubular sleeves at corners
- Scissors-shaped drawbar with safety handle with soft rubber grip and with an automatic damped retraction in resting position
- Load area covered with slip-resistant phenolic resin coated waterproof plywood
- Board walls 600 mm high, front walls screwed with platform, longitudinal walls can be hooked in and removed
- Board walls made of steel tube frames
- with welded-in
- wire grid 40 x 40 x 4 mm
- Load area =
- Length – 65 mm,
- Width – 5 mm.
- Automatic locking brake acting on the front wheels, according to EN 1757-3
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant



<b>Art. no.</b>	<b>50267 892</b>
<b>Brand</b>	FETRA
<b>Manufacturer Part Number</b>	6436V
<b>Length</b>	2350 mm
<b>Height</b>	1190 mm
<b>Loading surface length</b>	2000 mm
<b>Width</b>	1050 mm
<b>Loading-surface width</b>	1000 mm
<b>Loading surface size</b>	2000 x 1000 mm
<b>Loading-surface height</b>	490 mm
<b>Load-carrying capacity</b>	1250 kg
<b>Total stop optional</b>	No
<b>Wheel width</b>	80 mm
<b>Wheel diameter</b>	400 mm
<b>Material of wheel</b>	Solid rubber
<b>Gross Weight</b>	166.000 kg
<b>Product Group</b>	5AE

### EAN

4017976436005