

Pneumatic straight grinder SARH 830

260 watt



Application:

For milling, roughing and rough machining.

Execution:

- With double bearing of the drive spindle for particularly quiet running during milling work
- Controlled speed, for constant speeds and low air consumption when idling
- With energy-saving motor technology

Delivery:

With 6-mm collet chuck and key for changing tools, in box



Art. no.	75036 240
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150012015
Model	SARH 830
Valve design	Lever valve
Max. idle speed	30000 rpm
Power output	260 W
Air consumption	400 l/min
Connection thread	R 1/8 inch
Inner hose diameter	7 mm
Length	189 mm
Diameter of housing	31 mm
Max. clamping diameter	8 mm
Suitable for max. sanding block diameter	16 mm
Max. HM rotating milling cutter diameter	10 mm
Weight	0.52 kg
Gross Weight	0.901 kg
Product Group	748