



SITOR FUSE-LINK FOR SEMICONDUCTOR PROTECTION 50A GR, AC 690V, DC 700V SIZE 000, BRACKETS 80MM

Figure similar

Model		
product brand name		SETRON
Design of an identification indicator		front indicator
Design of the fuse link		SITOR, LV HRC design
General technical data		
Size of fuse system / acc. to DIN EN 60269-1		NH000
Operating class of the fuse link		gR
circuit-breaker / Design		3NE
Switching capacity		
<b>Switching capacity current</b>		
• for DC / acc. to IEC 60947-2 / Rated value	kA	50
• acc. to IEC 60947-2 / Rated value	kA	200
Dissipation		
<b>Active power loss</b>		
• for rated value of the current / with AC / in hot operating state / per pole	W	15
Electricity		
rated current I <sub>n</sub> / IEC, DIN/VDE / at 40 Cel	A	50
Current / with AC / Rated value	A	50
Mechanical Design		
mounting position		Any, preferably vertical
Environmental conditions		
Ambient temperature		

- minimum
- maximum

°C	-20
°C	50

### Certificates

#### Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F  
F

#### General Product Approval

#### Declaration of Conformity



### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NE87171>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3NE87171/all>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NE87171](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE87171)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015