

2 TERMINAL COVERS FOR 3-PHASE INFEED 50/70  
MM2 3RA6813-8AB/AC



General technical data:

<b>product brand name</b>		SIRIUS
<b>Product designation</b>		Terminal cover screw-type infeeds
<b>Protection class IP</b>		IP20
<b>Degree of pollution</b>		3
<b>Installation altitude at height above sea level maximum</b>	m	2 000
<b>Ambient temperature</b>		
• during transport	°C	-55 ... +80
• during storage	°C	-55 ... +80
• during operation	°C	-20 ... +60
<b>Vibration resistance</b>		f = 4 to 5.8 Hz; d = 15 mm; f = 5.8 to 500 Hz; a = 2 m / s <sup>2</sup> 10 cycles
<b>Shock resistance</b>		Semi-sinusoidal a = 6 m/s <sup>2</sup> at 10 ms; 3 pos. and 3 neg. Shock in all axes

Installation/ mounting/ dimensions:

<b>Mounting type</b>		snap-on mounting
<b>Width</b>	mm	70
<b>Height</b>	mm	60
<b>Depth</b>	mm	28

Certificates/ approvals:

General Product Approval	EMC	other
--------------------------	-----	-------



[Environmental Confirmations](#)

[other](#)

Safety related data:

Protection against electrical shock

finger-safe

Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA68803AB>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**


<http://support.automation.siemens.com/WW/view/en/3RA68803AB/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RA68803AB&lang=en>



last modified:



09.03.2015