

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: Hera GmbH & Co KG

Supplier's address: FE, Dieselstraße 9, 32130 Enger Herford, DE

Model identifier: LED IN-Stick H

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type (or other electric interface)	nein		
Mains or non-mains:	NMLS	Connected light source (CLS):	Nein
Colour-tuneable light source:	Nein	Envelope:	-
High luminance light source:	Nein		
Anti-glare shield:	Nein	Dimmable:	Only with specific dimmers

Product parameters

Parameter	Value	Parameter	Value
-----------	-------	-----------	-------

General product parameters:

Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	29	Energy efficiency class	G
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	1 517 in Wide cone (120°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000 or 4 000
On-mode power (P_{on}), expressed in W	27,5	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	95
Outer dimensions	Height	Spectral power distribution in the	See image in last page
	Width		
			34

without separate control gear, lighting control parts and non-lighting control parts, if any (millimetre)	Depth	13	range 250 nm to 800 nm, at full-load	
Claim of equivalent power ^(a)		-	If yes, equivalent power (W)	-
			Chromaticity coordinates (x and y)	0,376 0,375
Parameters for directional light sources:				
Peak luminous intensity (cd)		1	Beam angle in degrees, or the range of beam angles that can be set	100
Parameters for LED and OLED light sources:				
R9 colour rendering index value		0	Survival factor	0,00
the lumen maintenance factor		0,00		

(a) '-': not applicable;

(b) '-': not applicable;

