



SIMATIC DP, ELECTRONIC MODULE FOR ET 200S, 1 POS U, CONTROLLED POSITIONING WITH DIGITAL OUTPUTS FOR 5V/24V INCREMENTAL ENCODER, SSI-ENCODER, 30MM WIDE

Supply voltage

Load voltage L+

• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
• Reverse polarity protection	Yes

Input current

from load voltage L+ (without load), max.	55 mA
from backplane bus 3.3 V DC, max.	10 mA

Encoder supply

5 V encoder supply

• 5 V	No
-------	----

24 V encoder supply

• 24 V	Yes
• short-circuit protection	Yes
• Output current, max.	500 mA

Absolute encoder (SSI) encoder supply

• Absolute encoder (SSI)	Yes
• Type of output voltage	L+ (-0.8 V)
• Output current, max.	500 mA
• short-circuit protection	Yes

Power losses

Power loss, typ.	2 W
------------------	-----

Digital inputs	
Input characteristic curve in accordance with IEC 61131, type 2	Yes
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	-30 to +5V
• for signal "1"	+11 to +30V
Input current	
• for signal "0", max. (permissible quiescent current)	2 mA
• for signal "1", typ.	9 mA
Cable length	
• Unshielded, max.	50 m
Digital outputs	
short-circuit protection	Yes
• Response threshold, typ.	0.7 to 1.8 A
Limitation of inductive shutdown voltage to	Yes; L+ (-55 to 60 V)
Controlling a digital input	Yes
Switching capacity of the outputs	
• on lamp load, max.	5 W
Output voltage	
• Rated value (DC)	24 V
• for signal "0", max.	3 V
• for signal "1", min.	L+ (-1 V)
Output current	
• for signal "1" permissible range for 0 to 60 °C, min.	7 mA
• for signal "1" permissible range for 0 to 60 °C, max.	600 mA
• for signal "0" residual current, max.	0.3 mA
Output delay with resistive load	
• "0" to "1", max.	typically 150 µs
• "1" to "0", max.	typically 150 µs
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	2 Hz
• on lamp load, max.	10 Hz
Cable length	
• shielded, max.	1 000 m
• Unshielded, max.	600 m
Encoder	
Number of connectable encoders, max.	1

Connectable encoders	
• Incremental encoder (symmetrical)	Yes
• Incremental encoder (asymmetrical)	Yes
• Absolute encoder (SSI)	Yes
• 2-wire sensor	Yes; Type 2
Encoder signals, incremental encoder (symmetrical)	
Encoder signal 5 V	
— Signal level	to RS-422
— Terminating resistor	330 Ω
— Differential input voltage, min.	1 V
— Input frequency, max.	500 kHz
— Cable length, shielded, max.	50 m
Encoder signal 24 V	
— Rated value 24 V DC	Yes
— Input voltage for signal "0"	5 V
— Input voltage for signal "1"	30 V
— Input current for signal "0", max. (permissible quiescent current)	2 mA
— Input current for signal "1", typ.	9 mA
— Input frequency, max.	100 kHz
— Cable length, shielded, max.	50 m
Encoder signals, absolute encoder (SSI)	
• Cable length, shielded, max.	320 m at 125 kHz, 160 m at 250 kHz, 60 m at 500 kHz, 20 m at 1 MHz, 8 m at 2 MHz, twisted in pairs and shielded
• Monoflop time	64 μs
Updating the encoder value	
— Telegram runtime at 13 bit, min.	7 μs
— Telegram runtime at 25 bit, min.	13 μs
Response times	
Update time of the feedback messages	1 ms
Latch	In the case of incremental encoders: typ. 400 ms; in the case of SSI encoders: typ. 400 ms + age of the encoder value:
Response time at switchover/switchoff time	In the case of incremental encoders: output delay + 30 μs; in the case of SSI encoders: output delay + message frame runtime + 30 ms
Interrupts/diagnostics/status information	
Diagnostics indication LED	
• Actual value falling DN (green)	Yes
• Actual value rising UP (green)	Yes
• Positioning mode POS (green)	Yes
• Group error SF (red)	Yes
• Status indicator digital input (green)	Yes

Galvanic isolation

between backplane bus and all other circuit components	Yes
between the channels and backplane bus	Yes

Dimensions

Width	30 mm
Height	81 mm
Depth	52 mm

Weights

Weight, approx.	65 g
-----------------	------

last modified: 12.03.2015