

TWIN THERMOSTAT 0 TO 60 DEGREE C ZR 01172.0-00



Model		
product brand name		SIVACON
Product designation		twin thermostat
<b>Design of the switching function</b>		NC contact and NO contact
General technical data		
Operating temperature / minimum	°C	-45
<b>Mechanical service life (switching cycles) / typical</b>		100 000
Voltage		
<b>Inrush current / typical</b>	A	10
Main circuit		
Operating voltage / Rated value	V	250
Product details		
<b>Product component</b>		
• digital display		No
• hygrostat		No
Mechanical Design		
<b>Height</b>	mm	67
<b>Width</b>	mm	50
<b>Depth</b>	mm	46
<b>mounting position</b>		any
<b>Mounting type</b>		terminal mounting
<b>Material / of the enclosure</b>		plastic
Environmental conditions		

Relative humidity / Reference value	%	90
<b>Ambient temperature</b>		
• during storage / minimum	°C	-45
• during storage / maximum	°C	80

## Certificates

### Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

K

K

## General Product Approval



GOST



UL



## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21701E>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21701E/all>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8MR21701E](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR21701E)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015